



Metric table

Dimensions in: millimeters - inches

¹ d ₁ Thread	² l ₂	d ₂	l ₁	l ₃	l ₄	h ₁	h ₂
M 4	14 0.55	7.5 0.30	22 0.87	9.5 0.37	4.5 0.18	18.5 0.73	23 0.91
M 4	16 0.63	7.5 0.30	22 0.87	11.5 0.45	4.5 0.18	18.5 0.73	23 0.91
M 4	20 0.79	7.5 0.30	22 0.87	15.5 0.61	4.5 0.18	18.5 0.73	23 0.91
M 5	16 0.63	9 0.35	30 1.18	10 0.39	6 0.24	24.5 0.96	30.5 1.20
M 5	20 0.79	9 0.35	30 1.18	14 0.55	6 0.24	24.5 0.96	30.5 1.20
M 5	25 0.98	9 0.35	30 1.18	19 0.75	6 0.24	24.5 0.96	30.5 1.20
M 6	20 0.79	10.5 0.41	45 1.77	13.5 0.53	6.5 0.26	24.5 0.96	35 1.38
M 6	25 0.98	10.5 0.41	45 1.77	18.5 0.73	6.5 0.26	24.5 0.96	35 1.38
M 6	30 1.18	10.5 0.41	45 1.77	25.5 1.00	6.5 0.26	24.5 0.96	35 1.38
M 6	32 1.26	10.5 0.41	45 1.77	25.5 1.00	6.5 0.26	24.5 0.96	35 1.38

Specification

- Lever body
Zinc die-cast
Powder coated
Silver, RAL 9006, textured finish
- Threaded stud / spacer bushing
Stainless steel AISI 303
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

GN 511 adjustable lever kits replace the DIN 912 socket cap screws in mounting clamps. It is used on all clamping points where repeated clamping actions are required, e.g. for adjusting a stop mechanism. The matching adjustable lever kits for each clamping thread are listed in the dimensional tables of the mounting clamps.

How to order ¹ ² GN 511-M5-25	1 Thread d ₁
	2 Length l ₂

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

