



SS Stainless Steel

3 Type

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side

Metric table

| d₁ | l₁ ±0.5 Type A | ±0.3 Type B Tapped hole for mounting stud | d₂ Thread | d₃ | h | l₂ | r ≈ | t₁ | t₂ |
|----------------------|-------------------------------------|--|--------------------------------|----------------------|------------|----------------------|------------|----------------------|----------------------|
| 20 .79 | 200 7.87 | 200 7.87 | M 8 | - | 68 2.68 | 20 .79 | 22 .87 | 15 .59 | - |
| 20 .79 | 250 9.84 | 250 9.84 | M 8 | - | 68 2.68 | 20 .79 | 22 .87 | 15 .59 | - |
| 20 .79 | 300 11.81 | 300 11.81 | M 8 | - | 68 2.68 | 20 .79 | 22 .87 | 15 .59 | - |
| 20 .79 | 350 13.78 | 350 13.78 | M 8 | - | 68 2.68 | 20 .79 | 22 .87 | 15 .59 | - |
| 28 1.10 | 250 9.84 | 250 9.84 | M 10 | 32 1.26 | 90 3.54 | 20 .79 | 32 1.26 | - | 17 .67 |
| 28 1.10 | 300 11.81 | 300 11.81 | M 10 | 32 1.26 | 90 3.54 | 20 .79 | 32 1.26 | - | 17 .67 |
| 28 1.10 | 350 13.78 | 350 13.78 | M 10 | 32 1.26 | 90 3.54 | 20 .79 | 32 1.26 | - | 17 .67 |
| 28 1.10 | 400 15.75 | 400 15.75 | M 10 | 32 1.26 | 90 3.54 | 20 .79 | 32 1.26 | - | 17 .67 |

Dimensions in: millimeters - inches

Specification

- Stainless steel
European Standard No. 1.4301 (AISI 304),
matte shot-blasted finish
d₁ = 20: solid material
d₁ = 28: tube Ø 28x2 mm
- Tapped insert / mounting stud
Stainless steel
European Standard No. 1.4305 (AISI 303)
- Set screw (Type B)
d₁= 20: DIN 914-M5-6-NI
d₁= 28: DIN 914-M6-8-NI
- RoHS compliant

Information

GN 426.5 cabinet "U" handles can be mounted from the back (type A) as well as from the operator's side (type B). In this case the stud is first screwed in from the machine side and then the handle is pushed on and secured with the set screw.

Both mounting methods allow the mounting of a pair of handles in opposite position. This method could be used e.g. on doors (double handle). In general, a mounting stud with special length l₂ might be required.

The manufacturing process (bending) allows the production of special lengths in relatively small quantities.

see also...

- Cabinet "U" Handles GN 426 (Aluminum)
- Tubular Grip Handles GN 666.5 / GN 666.7 (Stainless Steel)

On request

- Special lengths
- Various metric size fasteners and kit packaging

| | | |
|---|---|--------------------------------------|
| <p>How to order</p> <p>GN 426.5-28-400-A</p> | 1 | Handle diameter d₁ |
| | 2 | Length l₁ |
| | 3 | Type |