



**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub> +0.5	<b>2</b> d <sub>2</sub> Thread	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub> min.	l <sub>3</sub>
26 1.02	M 8	21 0.83	80 3.15	40 1.57	7 0.28

**Specification**

- Plastic  
Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 230 °F (110 °C)
  - Black-gray, RAL 7021, matte finish
  - White, RAL 9016, matte finish
- Plastic Characteristics → page 2135
- RoHS compliant



**Information**

EN 519.2 cylindrical handles are manufactured from an antibacterial plastic.

Adding a silver-based substance has created a natural active agent that helps to prevent the growth of bacteria. Even after repeated cleaning with soap or solvent, the antibacterial effect of this additive will not diminish.

With these properties, operating parts made of this plastic are the perfect choice for use in medical engineering, in the food and the pharmaceutical industry, and in general wherever hygiene is of great importance.

see also...

- Product Family Sanline → page 2131
- Cylindrical Handles EN 519.2 (Technopolymer Plastic) → [www.jwwinco.com](http://www.jwwinco.com)
- Cylindrical Handles EN 519 (Phenolic Plastic) → page 62
- Softline Cylindrical Handles EN 519.6 → [www.jwwinco.com](http://www.jwwinco.com)

<b>How to order</b> <b>EN 519.2-26-M8-SGA</b>	<b>1</b>	Handle diameter d <sub>1</sub>
	<b>2</b>	Thread d <sub>2</sub>
	<b>3</b>	Color

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4