




Metric table

| Dimensions in: millimeters / inches |                                  |               |                                                    |                |                |                |                |                |            |                |                |
|-------------------------------------|----------------------------------|---------------|----------------------------------------------------|----------------|----------------|----------------|----------------|----------------|------------|----------------|----------------|
| d <sub>1</sub>                      | l <sub>1</sub><br>±0.5<br>Type A |               | ±0.3<br>Type B<br>Tapped hole for<br>mounting stud | d <sub>2</sub> | d <sub>3</sub> | h <sub>1</sub> | h <sub>2</sub> | l <sub>2</sub> | r ≈        | t <sub>1</sub> | t <sub>2</sub> |
| 20<br>0.79                          | 200<br>7.87                      | 200<br>7.874  | M 8                                                | -              | 105<br>4.13    | 68<br>2.68     | 20<br>0.79     | 22<br>0.87     | 15<br>0.59 | -              | -              |
| 20<br>0.79                          | 300<br>11.81                     | 300<br>11.811 | M 8                                                | -              | 105<br>4.13    | 68<br>2.68     | 20<br>0.79     | 22<br>0.87     | 15<br>0.59 | -              | -              |
| 28<br>1.10                          | 250<br>9.84                      | 250<br>9.843  | M 10                                               | 32<br>1.26     | 128<br>5.04    | 90<br>3.54     | 20<br>0.79     | 32<br>1.26     | -          | 17<br>0.67     | -              |
| 28<br>1.10                          | 350<br>13.78                     | 350<br>13.780 | M 10                                               | 32<br>1.26     | 128<br>5.04    | 90<br>3.54     | 20<br>0.79     | 32<br>1.26     | -          | 17<br>0.67     | -              |
| 28<br>1.10                          | 500<br>19.69                     | 500<br>19.685 | M 10                                               | 32<br>1.26     | 128<br>5.04    | 90<br>3.54     | 20<br>0.79     | 32<br>1.26     | -          | 17<br>0.67     | -              |

Specification

Handle

- Stainless steel AISI 304
- d<sub>1</sub> = 20 mm: Solid material
  - d<sub>1</sub> = 28 mm: Tube Ø 28 x 2 mm
  - Matte shot-blasted finish

Tapped insert for d<sub>1</sub> = 28mm

Stainless steel AISI 303

Mounting stud

Stainless steel AISI 303

Set screw (Type B)

- Stainless steel
- d<sub>1</sub> = 20 mm: DIN 914-M5-6-NI
  - d<sub>1</sub> = 28 mm: DIN 914-M6-8-NI

RoHS

Cabinet U-handles GN 426.6 can be mounted from the back (type A) as well as from the operator's side (type B). In this case the stud is first screwed in from the machine side and then the handle is pushed on and secured with the set screw.

Both mounting methods allow the mounting of a pair of handles in opposite position. This method could be used e.g. on doors (double handle). In general, a mounting stud with special length l<sub>2</sub> might be required.

| see also...                                                                             | Page |
|-----------------------------------------------------------------------------------------|------|
| GN 425.1 Cabinet U-Handles<br>(Ø 8, 10, 12 mm, Offset Round Aluminum / Stainless Steel) | QVX  |

| Technical Information           | Page |
|---------------------------------|------|
| Load Capacity Information       | QVX  |
| Stainless Steel Characteristics | QVX  |

| How to order      | 1 | Handle diameter d <sub>1</sub> |
|-------------------|---|--------------------------------|
|                   | 2 | Length l <sub>1</sub>          |
|                   | 3 | Type                           |
| GN 426.6-20-300-A |   |                                |