



Assembly examples



as spacer disk



as foot disk



Metric

SS Stainless Steel

**4 Type**

- A Mounting via mounting hole
- B Mounting via adhesive pad

**Metric table**

1		2		3				Dimensions in: millimeters - inches	
d <sub>1</sub>	h	d <sub>2</sub> +0.5	d <sub>3</sub> +0.5	s <sub>1</sub>	s <sub>2</sub>				
19 0.75	3 0.12	7 0.28	14 0.55	4 0.16	7.5 0.30	1.5 0.06	1.1 0.04		
25 0.98	3 0.12	8 0.31	16 0.63	4 0.16	7.5 0.30	1.5 0.06	1.1 0.04		
32 1.26	4 0.16	9 0.35	18 0.71	5 0.20	9 0.35	2 0.08	1.1 0.04		
38 1.50	4 0.16	10 0.39	20 0.79	5 0.20	9 0.35	2 0.08	1.1 0.04		
50 1.97	5 0.20	11 0.43	22 0.87	6 0.24	11 0.43	2.5 0.10	1.1 0.04		
64 2.52	5 0.20	13 0.51	26 1.02	6 0.24	11 0.43	2.5 0.10	1.1 0.04		

**Specification**

- **GN 438**  
Plate  
Steel, zinc plated, blue passivated finish
- **GN 438.5**  
Plate  
Stainless steel  
European Standard No. 1.4301 (AISI 304)
- Rubber pad  
Acrylonitrile butadiene rubber (NBR)  
- Vulcanized  
- Black  
- Temperature resistant up to 248 °F (120 °C)  
- Hardness shore A **70**
- Adhesive pad (only type B)  
Scotch Mount TM 5952  
- Double-sided  
- Acrylate adhesive core
- RoHS compliant

**On request**

- Other shore hardnesses

**Information**

GN 438 and GN 438.5 rubber spacer disks provide a damping and noise reducing effect and protect surfaces from damage.

By stacking several spacer disks on each other, the spring rate of the package can be increased, which opens up new possibilities for use.

When used as a foot disk, the type A version with mounting hole can be installed on small machines, systems or devices using screws bearing in mind the height of the screw head. Alternatively, after the protective film has been removed, the type B can be adhered to all suitable and clean surfaces by means of the adhesive pad.

see also...

- *Vibration / Shock Absorption Mounts GN 454*

How to order (Steel plate)	1 Outer diameter d <sub>1</sub>
	2 Height h
	3 Inner diameter d <sub>2</sub>
	4 Type
	5 Hardness

1 2 3 4 5  
**GN 438-25-16-4-A-70**

How to order (Stainless steel plate)	1 Outer diameter d <sub>1</sub>
	2 Height h
	3 Inner diameter d <sub>2</sub>
	4 Type
	5 Hardness

1 2 3 4 5  
**GN 438.5-64-26-6-B-70**