



Inch table

Dimensions in: inches - millimeters											
d ₁	d ₂ Bore		d ₃ Thread	d ₄	d ₅	d ₆	t	b	l ₁	l ₂	l ₃
1.97 50	B 5/16	Blank	5/16 x 18	.79 20	.71 18	5.00 127	0.5	.51 13	.83 21	1.14 29	.39 10
2.76 70	B 3/8	Blank	3/8 x 16	1.18 30	1.10 28	7.13 181	0.8	.71 18	.98 25	1.30 33	.47 12
3.15 80	B 1/2	Blank	1/2 x 13	1.38 35	1.34 34	7.13 181	0.8	.75 19	1.18 30	1.57 40	.59 15
3.94 100	B 1/2	Blank	-	1.42 36	1.34 34	8.43 214	1.5	.79 20	1.34 34	1.73 44	.55 14
5.12 130	B 1/2	Blank	-	1.57 40	1.42 36	8.43 214	1.5	.87 22	1.34 34	1.85 47	.51 13

Specification

- Plastic
Duroplast (Phenolic PF)
 - High strength reinforced
 - Temperature resistant up to 230 °F (110 °C)
 - Black, glossy finish
- Hub bushing
Steel, blackened finish, molded-in
- RoHS compliant

Information

EN 527 control knobs with a multi-lobed rim are very sturdy control knobs which can be used either as control knobs or for clamping purposes.

Worth mentioning is the deliberately large hub. They also lend themselves to applications where a large contact face or a large bore is required.

Resistant to solvents, oils, grease and other chemical agents.

On request

- Blank version with brass hub
- Other modifications such as special inch and metric blind bores, special threads, etc.

How to order	1	Knob diameter d ₁
	2	Thread d ₃ (Bore diameter d ₂)

EN 527-50-5/16X18