

SS Stainless Steel

**4 Type (Base)**

- D0 Without rubber pad / cap
- D1 With rubber cap, clipped on, black
- D3 With rubber pad, vulcanized, black


**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>				Version T / TK						
		Version S / SK										
50 1.97	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-
50 1.97	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-
50 1.97	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-
50 1.97	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-
60 2.36	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-
60 2.36	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-
60 2.36	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-
60 2.36	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-
80 3.15	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-
80 3.15	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-
80 3.15	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-
80 3.15	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-
80 3.15	M 20	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-
80 3.15	M 24	-	-	-	-	100 3.94	125 4.92	150 5.91	200 7.87	300 11.81	-	-


d <sub>1</sub>	d <sub>2</sub>			d <sub>3</sub>	h <sub>1</sub>	h <sub>3</sub>	h <sub>4</sub>	h <sub>6</sub>	l <sub>8</sub>	m	r	s	A/F <sub>1</sub>	A/F <sub>2</sub>
50 1.97	M 8	M 10	M 12	13 0.51	2.5 0.10	11 0.43	-	4 0.16	60 2.36	45 1.77	15 0.59	2 0.08	17 0.67	-
50 1.97	M 16	-	-	13 0.51	2.5 0.10	-	17 0.67	4 0.16	60 2.36	45 1.77	15 0.59	2 0.08	-	12 0.47
60 2.36	M 8	M 10	M 12	13 0.51	2.5 0.10	11 0.43	-	4.5 0.18	65 2.56	50 1.97	15 0.59	2 0.08	17 0.67	-
60 2.36	M 16	-	-	13 0.51	2.5 0.10	-	17 0.67	4.5 0.18	65 2.56	50 1.97	15 0.59	2 0.08	-	12 0.47
80 3.15	M 8	M 10	M 12	13 0.51	3 0.12	12 0.47	-	5 0.20	85 3.35	70 2.76	15 0.59	2 0.08	17 0.67	-
80 3.15	M 16	-	-	13 0.51	3 0.12	-	18 0.71	5 0.20	85 3.35	70 2.76	15 0.59	2 0.08	-	12 0.47
80 3.15	M 20	-	-	13 0.51	3 0.12	-	19 0.75	5 0.20	85 3.35	70 2.76	15 0.59	2 0.08	-	15 0.59
80 3.15	M 24	-	-	13 0.51	3 0.12	-	22 0.87	5 0.20	85 3.35	70 2.76	15 0.59	2 0.08	-	19 0.75

### Stud versions



**S** Without nut  
**SK** With nut

External hex at the bottom at d<sub>2</sub>  
M 8, M 10, M 12



**T** Without nut  
**TK** With nut

Wrench flat at the bottom at d<sub>2</sub>  
M 16, M 20, M 24

### Specification


- Base  
Stainless steel AISI 316L  
Plain, tumbled finish
- Threaded stud  
Stainless steel AISI 316L
- Hex nut ISO 4032  
Stainless steel AISI 316L
- Rubber cap  
TPE (Santoprene®) ≈ 80 shore A  
- Clipped on  
- Black
- Rubber pad  
NBR (Perbunan®) 70 ±5 shore A  
- Vulcanized, non-skid  
- Black
- Load Rating Information → page 2121
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

### Information

GN 45 leveling feet are intended for use in aggressive environments. The wide range of possible combinations of the base and the stud / socket versions make these leveling feet universally applicable. The leveling feet can be screwed to the mounting surface using the mounting hole, which prevents lateral slippage. The base with rubber pad / cap also protects sensitive surfaces. These leveling feet are supplied fully assembled and cannot be disassembled.

see also...

- Leveling Feet GN 40 (Steel, without Mounting Hole) → page 1516
- Leveling Feet GN 42 (Steel, with Mounting Hole) → page 1526
- Leveling Feet GN 42 (Steel, with Slotted Mounting Hole, Rectangular Shape) → page 1526
- Leveling Feet GN 41 (Stainless Steel AISI 304, without Mounting Hole) → page 1520
- Leveling Feet GN 43 (Stainless Steel AISI 304, with Mounting Hole) → page 1532
- Leveling Feet GN 43 (Stainless Steel AISI 304, with Slotted Mounting Hole, Rectangular Shape) → page 1536
- Leveling Feet GN 44 (Stainless Steel AISI 316L, without Mounting Hole) → page 1524

<p>How to order</p>  <p><b>GN 45-50-M10-60-D3-SK</b></p>	<b>1</b> Base diameter d <sub>1</sub>
	<b>2</b> Thread d <sub>2</sub>
	<b>3</b> Length l <sub>1</sub>
	<b>4</b> Type (Base)
	<b>5</b> Stud version

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

