



ELESA original design B.193-p / B.193-p-SST



**Metric table**

Dimensions in: millimeters - inches

1		2		2		3					d <sub>3</sub>	h	k
d <sub>1</sub>	d <sub>2</sub> Thread EN 529	d <sub>2</sub> Thread EN 529.5	Length l										
15 .59	M 3	M 4	M 3	M 4	6 .24	10 .39	16 .63	-	-	-	11 .43	11 .43	8 .31
15 .59	M 5	-	M 5	-	10 .39	16 .63	25 .98	-	-	-	11 .43	11 .43	8 .31
18 .71	M 5	-	M 5	-	10 .39	16 .63	25 .98	40* 1.57	-	-	13 .51	12 .47	9 .35
22 .87	M 6	-	M 6	-	10 .39	16 .63	20 .79	25 .98	30 1.18	40* 1.57	15 .59	14 .55	9 .35
25 .98	M 6	M 8	M 6	-	16 .63	25 .98	-	-	-	-	18 .71	18 .71	12 .47
30 1.18	M 8	-	M 8	-	16 .63	25 .98	40 1.57	-	-	-	24 .94	18 .71	12 .47
35 1.38	M 8	-	-	-	25 .98	40 1.57	-	-	-	-	27 1.06	23 .91	20 .79

\* These sizes are only available for EN 529

**Specification**

- Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 230 °F (110 °C)  
- Black, shiny finish
- **EN 529**  
Threaded stud  
Steel, zinc plated, blue passivated finish
- **EN 529.5**  
Threaded stud  
Stainless steel  
European Standard No. 1.4305 (AISI 303)
- RoHS compliant

**Information**

The surface quality of EN 529 and EN 529.5 knurled screws is of a sufficiently high standard to meet the highest requirements. Flash marks are not visible.  
Duroplast material is highly resistant to chemicals.

How to order (Steel threaded stud) 1 2 3 <b>EN 529-25-M8-16</b>	1	Handle diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>
	3	Length l
How to order (Stainless steel threaded stud) 1 2 3 <b>EN 529.5-18-M5-16</b>	1	Handle diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>
	3	Length l

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4