



**SS** Stainless Steel

**Metric table**



Dimensions in: millimeters - inches

d <sub>1</sub> Thread	d <sub>2</sub>	d <sub>3</sub>	h	k
M 2	9 0.35	4.5 0.18	5.3 0.21	2 0.08
M 2.5	11 0.43	5 0.20	6.5 0.26	2.5 0.10
M 3	12 0.47	6 0.24	7.5 0.30	2.5 0.10
M 4	16 0.63	8 0.31	9.5 0.37	3.5 0.14
M 5	20 0.79	10 0.39	11.5 0.45	4 0.16
M 6	24 0.94	12 0.47	15 0.59	5 0.20
M 8	30 1.18	16 0.63	18 0.71	6 0.24
M 10	36 1.42	20 0.79	23 0.91	8 0.31
M 12	40 1.57	22 0.87	25 0.98	10 0.39

**Specification**



- Steel
  - Property class 5
  - Visible face fine turned
  - Blackened finish
  - Zinc plated, blue passivated finish
- Stainless steel AISI 303
  - Matte shot-blasted finish
- RoHS compliant

—  
**ZB**

**NI**

**Information**

DIN 466 knurled nuts can be tightened and loosened easily without tools.

see also...

- Knurled Nuts GN 536 (Stainless Steel)
- Knurled Nuts DIN 6303 (Stainless Steel)
- Flat Knurled Nuts DIN 467
- Knurled Nuts DIN 466 with Loss Protection GN 111.7

How to order (Steel, blackened finish)	1 Thread d <sub>1</sub>
<b>DIN 466-M6</b>	
How to order (Steel, zinc plated)	1 Thread d <sub>1</sub>
<b>DIN 466-M10-ZB</b>	2 Finish
How to order (Stainless steel)	1 Thread d <sub>1</sub>
<b>DIN 466-M2-NI</b>	2 Material