




Inch table

1

2

Dimensions in: inches / millimeters

l_1	d_1			d_2	d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
1.65 42	10 x 24	10 x 32	1/4 x 20	0.47 12	0.71 18	0.63 16	1.06 27	0.24 6	1.26 32	0.14 3.5	0.39 10
2.48 63	1/4 x 20	5/16 x 18	-	0.59 15	0.91 23	0.79 20	1.34 34	0.31 8	1.69 43	0.16 4	0.55 14
3.15 80	5/16 x 18	3/8 x 16	1/2 x 13	0.75 19	1.10 28	0.94 24	1.65 42	0.39 10	2.13 54	0.16 4	0.67 17
3.94 100	3/8 x 16	1/2 x 13	-	0.98 25	1.30 33	1.22 31	1.89 48	0.47 12	2.56 65	0.20 5	0.79 20

Metric table

1

2

Dimensions in: millimeters / inches

l_1	d_1			d_2	d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
42 1.65	M 5	M 6	-	12 0.47	18 0.71	16 0.63	27 1.06	6 0.24	32 1.26	3.5 0.14	10 0.39
63 2.48	M 6	M 8	-	15 0.59	23 0.91	20 0.79	34 1.34	8 0.31	43 1.69	4 0.16	14 0.55
80 3.15	M 8	M 10	M 12	19 0.75	28 1.10	24 0.94	42 1.65	10 0.39	54 2.13	4 0.16	17 0.67
100 3.94	M 10	M 12	M 14	M 16	25 0.98	33 1.30	31 1.22	48 1.89	12 0.47	65 2.56	5 0.20

Specification

Lever body

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature
-22 °F to +248 °F (-30 °C to +120 °C)
- Black, RAL 9005, matte finish

● SW

Push button

Plastic, black matte finish

Insert

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Black
- Tapped insert
- Brass

RoHS

On request

- With stainless steel tapped insert
- Other colors

Adjustable levers EN 503 have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged. Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the mating serrations of the lever and the insert automatically re-engage via a spring and push button that holds the assembly together.

Push button solution offers absolute electrical insulation for the operator, no visible steel parts subject to rust, and is a comfortable lever release mechanism.

Resistant to solvents, oils, grease and other chemical agents.

Technical Information	Page
Plastic Characteristics	QVX

How to order (Inch) 1 2 3 EN 503-42-10X24-SW	1 Lever length l_1
	2 Thread d_1
	3 Color
How to order (Metric) 1 2 3 EN 503-80-M10-SW	1 Lever length l_1
	2 Thread d_1
	3 Color