



ELESA original design VTR.

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂ Thread	Length l			d ₃	h ₁	h ₂	t
		10	20	40				
32 1.26	M 5	.39	.79	1.57	.55	1.02	.63	.39
32 1.26	M 6	.39	.79	1.57	.55	1.02	.63	.47
40 1.57	M 6	.39	.79	1.57	.63	1.18	.67	.47
40 1.57	M 8	.63	1.18	1.97	.63	1.18	.67	.55
50 1.97	M 8	.63	1.18	1.97	.75	1.38	.75	.55
50 1.97	M 10	.79	1.18	1.97	.75	1.38	.75	.63
60 2.36	M 10	.79	1.18	1.97	.87	1.61	.87	.63
60 2.36	M 12	.79	1.18	1.97	.87	1.61	.87	.71

Specification

- Triangular knob
Plastic
Technopolymer (Polyamide PA)
Temperature resistant up to
194 °F (90 °C)

- Color (shiny finish):
 - Black, RAL 9005 ● SW
 - Orange, RAL 2004 ● OR
 (only available for tapped insert type)

- Tapped insert
Brass

- Threaded stud
Steel, zinc plated, blue passivated finish

- RoHS compliant (only color SW)

Information

EN 5339 triangular knobs offer an elegant shape and a bright finish.

How to order (Tapped insert) EN 5339-40-M8-OR	1	Handle diameter d ₁
	2	Thread d ₂
	4	Color

How to order (Threaded stud) EN 5339-50-M10-30-SW	1	Handle diameter d ₁
	2	Thread d ₂
	3	Length l
	4	Color