



Metric table

¹ d ₁	² d ₂ Thread	³ Length l	d ₃	h ₁	h ₂
63 2.48	M 8	25 0.98	23 0.91	30.5 1.20	16 0.63
80 3.15	M 10	30 1.18	30.5 1.20	37 1.46	20 0.79
100 3.94	M 12	40 1.57	35 1.38	43 1.69	23 0.91

Dimensions in: millimeters - inches

Specification

- Three-lobed knob
Plastic
Technopolymer (Polyamide PA)
- Coated with a soft elastomer (TPE)
70 Shore A
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black, matte finish
- Softline coating is chemically bonded with the plastic core
- Threaded stud
Steel zinc plated, blue passivated finish
- Color of the cover cap (matte finish):

● DSW	Black, RAL 9005
● DOR	Orange, RAL 2004
● DGR	Gray, RAL 7035
● DGB	Yellow, RAL 1021
● DBL	Blue, RAL 5024
● DRT	Red, RAL 3000
● DGN	Green, RAL 6017
- [Elastomer Characteristics](#) → page QVX
- [Plastic Characteristics](#) → page QVX
- [RoHS compliant](#)

Information

The Softline coating of the EN 533.6 three-lobed knobs with threaded stud makes these operating elements particularly “operator friendly” and hence ergonomic.

The soft, non-slip coating improves the contact in both moist (hand perspiration) and in dry conditions, with oily surfaces and at high or very low temperatures.

The use of Softline star knobs is recommended particularly when heavy duty clamping is required.

see also...

- [Three-Lobed Knobs GN 5345](#) → page QVX
- [Three-Lobed Knobs EN 5330 \(Plastic\)](#) → page QVX

How to order	
¹	Handle diameter d ₁
²	Thread d ₂
³	Length l
⁴	Color of the cover cap

EN 533.6-63-M8-25-DBL