



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	² s H9 Square	d ₃	d ₄	h ₁	h ₂	t
32 1.26	M 5	V 5	14 0.55	10 0.39	14 0.55	4 0.16	6 0.24
40 1.57	M 6	V 6	16 0.63	12 0.47	18 0.71	5 0.20	8 0.31
50 1.97	M 8	V 6	19 0.75	16 0.63	22 0.87	6 0.24	10 0.39
60 2.36	M 10	V 7	22 0.87	20 0.79	26 1.02	7 0.28	12 0.47

Specification

- Triangular knob
Plastic
Technopolymer (Polyamide PA)
- Temperature resistant up to 194 °F (90 °C)
- Black, shiny finish
- Tapped insert
Brass
- ISO Fundamental Tolerances → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

Information

EN 5341 triangular knobs offer an elegant shape and a bright finish.
Due to the shock proof technopolymer material used, it eliminates the use of a metal insert on the square knob.
see also...
• Five-Lobed Knobs EN 5331 (Low Type) → page QVX

How to order ¹ ² EN 5341-32-V5	1 Handle diameter d ₁
	2 Square s (Thread d ₂)

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

