



- 3 Type**
- S** With socket cap screw DIN 912
 - K** With adjustable lever kit

Metric table

Dimensions in: millimeters - inches

1 d ₁ Thread	2 l ₂	d ₂	d ₃	d ₄	l ₁	l ₃	l ₄	l ₅	l ₆	h ₁	h ₂	Swivel mounting clamp k dimension
M 4	16 0.63	7.5 0.30	6.9 0.27	7.5 0.30	22 0.87	11.5 0.45	4.5 0.18	4 0.16	4 0.16	18.5 0.73	23 0.91	16 0.63
M 5	20 0.79	9 0.35	8.4 0.33	9 0.35	30 1.18	14 0.55	6 0.24	5 0.20	5 0.20	24.5 0.96	30.5 1.20	20 0.79
M 6	25 0.98	10.5 0.41	9.9 0.39	10.5 0.41	45 1.77	18.5 0.73	6.5 0.26	7 0.28	6 0.24	24.5 0.96	35 1.38	25 0.98
M 6	30 1.18	10.5 0.41	9.9 0.39	10.5 0.41	45 1.77	23.5 0.93	6.5 0.26	7 0.28	6 0.24	24.5 0.96	35 1.38	30 1.18

Specification

- Lever body
Zinc die-cast
Powder coated
Silver, RAL 9006, textured finish
- Threaded stud / spacer bushing / centering bushing / threaded bushing
Stainless steel AISI 303
- Socket cap screw DIN 912
Stainless steel AISI 304
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

Information

With GN 511.1 clamping kits GN 482 swivel mounting clamps, GN 483 T-swivel mounting clamps as well as GN 484 attachment swivel mountings clamps with the same k dimensions can be combined to mounting clamp joints.

The centering bushing positions and supports the swivel mounting clamps in relation to each other. During assembly, the knurled threaded bushing is inserted by the clamping screw itself or by pressing into one of the two swivel mounting clamps and is then used to clamp the joint.

The appropriate clamping kits are indicated in the dimensional tables of the various swivel mounting clamps.

<p>How to order</p> <p>GN 511.1-M5-20-S</p>	1	Thread d ₁
	2	Length l ₂
	3	Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10