




Metric



Metric table

Dimensions in: millimeters / inches

| ¹ d ₁ | ² d ₂ | d ₃ | d ₄ | h ₁ | h ₂ | t min. |
|-----------------------------|-----------------------------|----------------|----------------|----------------|----------------|------------|
| 40 1.57 | M 6 | 18 0.71 | 18.8 0.74 | 30.5 1.20 | 15 0.59 | 12 0.47 |
| 40 1.57 | M 8 | 18 0.71 | 18.8 0.74 | 30.5 1.20 | 15 0.59 | 15 0.59 |
| 50 1.97 | M 8 | 21 0.83 | 21.8 0.86 | 34 1.34 | 17 0.67 | 15 0.59 |
| 50 1.97 | M 10 | 21 0.83 | 21.8 0.86 | 34 1.34 | 17 0.67 | 18 0.71 |

Specification

Star knob

Stainless steel AISI 316L

- Matte finish (Ra < 0.8 µm)
- Polished finish (Ra < 0.8 µm)

MT
PL

Sealing ring

- HNBR **H**
- Operating temperature
-13 °F to +302 °F (-25 °C to +150 °C)
- EPDM **E**
- Operating temperature
-40 °F to +248 °F (-40 °C to +120 °C)
- FKM **F**
- Operating temperature
23 °F to 392 °F (-5 °C to +200 °C)
- FDA compliant material
- Blue
- Hardness 85±5 Shore A

RoHS

Star knobs GN 5435 are intended for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish and the large corner radii prevent adherence of dirt and facilitate cleaning.

see also...

| | Page |
|---|------|
| GN 5445 Three-Lobed Knobs (Stainless Steel, Hygienic Design) | QVX |
| GN 305 Adjustable Levers (Stainless Steel, Hygienic Design) | QVX |

Technical Information

| | |
|---------------------------------|-----|
| Product Family Hygienic Design | QVX |
| Plastic Characteristics | QVX |
| Stainless Steel Characteristics | QVX |

Accessory

| | |
|------------------------------|-----|
| GN 7600 Sealing Rings | QVX |
|------------------------------|-----|

How to order

GN 5435-40-M8-PL-H

| | |
|--------------|--------------------------------|
| ¹ | Handle diameter d ₁ |
| ² | Thread d ₂ |
| ³ | Finish |
| ⁴ | Sealing ring material |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

