



ELESA Original design T.440 / T.440a

2 Type

- A** Without dipstick
- B** With dipstick

Metric table



Dimensions in: millimeters - inches

d ₁ Thread	d ₂	l ₁	l ₂	l ₃
G 1/4	20.5 <i>0.81</i>	9 <i>0.35</i>	19 <i>0.75</i>	192 <i>7.56</i>
G 3/8	25 <i>0.98</i>	9 <i>0.35</i>	21 <i>0.83</i>	192 <i>7.56</i>
G 1/2	28 <i>1.10</i>	11 <i>0.43</i>	25 <i>0.98</i>	189 <i>7.44</i>
G 3/4	34 <i>1.34</i>	12 <i>0.47</i>	27 <i>1.06</i>	188 <i>7.40</i>
G 1	42 <i>1.65</i>	13 <i>0.51</i>	29 <i>1.14</i>	188 <i>7.40</i>
G 1 1/4	52 <i>2.05</i>	13 <i>0.51</i>	32 <i>1.26</i>	185 <i>7.28</i>
G 1 1/2	57 <i>2.24</i>	13 <i>0.51</i>	35 <i>1.38</i>	185 <i>7.28</i>

Specification

- Fluid plug
Plastic
Technopolymer (Polyamide PA)
- Black, matte finish
- Temperature resistant up to 212 °F (100 °C)
- Seal
NBR rubber (Perbunan®)
- Dipstick
Steel, phosphated
- RoHS compliant

Information

For thread sizes larger than G 1/2, EN 548.1 fluid plugs have a radial undercut where the seal is seated in that recess. The recessed groove prevents the seal from being deformed when tightening the fluid plug. MIN-MAX lines can easily be marked on the two flat sides of the dipstick.

see also...

- Threaded plugs GN 441 (with Finger Grip)

<p>How to order</p> <p>EN548.1- G¹/₂ -B</p>	1 Thread d ₁
	2 Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

