



ELESA original design I.680 SOFT



Metric table

Dimensions in: millimeters - inches

¹ d ₁ +0.5	² d ₂ Thread	d ₃	l ₁	l ₂ min.	l ₃
24 .94	M 8	20.5 .81	65 2.56	30 1.18	7 .28
24 .94	M 10	20.5 .81	65 2.56	40 1.57	7 .28
26 1.02	M 8	21 .83	80 3.15	40 1.57	7 .28
26 1.02	M 10	21 .83	80 3.15	55 2.17	7 .28
26 1.02	M 12	21 .83	80 3.15	55 2.17	7 .28
28 1.10	M 10	22 .87	90 3.54	56 2.20	7 .28
28 1.10	M 12	22 .87	90 3.54	58 2.28	10 .39

Specification

- Plastic
Technopolymer (Propylene PP)
- Softline coating
Elastomer (TPE) 70 shore A
- Chemically bonded with the plastic core
- With FDA admission
- Temperature resistant up to 175 °F (80 °C)
- Black, matte finish
- Molded-in thread

• RoHS compliant

Information

The softline coating of EN 519.6 cylindrical handles makes them ergonomically operator friendly. The soft, antislip contact surface is very user friendly. It improves the contact between a damp (perspiration) or dry hand, or an oily surface, whether in a cold or hot environment.

see also...

- Product Range Softline
- Cylindrical Handles EN 519
- Cylindrical Handles EN 519.1 (Press-On Type)

<p>How to order</p> <p>¹ ²</p> <p>EN 519.6-24-M8</p>	1	Handle diameter d ₁
	2	Thread d ₂