




Metric

elesa

Original design I.701+x / I.731+x

4

Type

A Without finger molding

B With finger molding

Metric table

Dimensions in: millimeters / inches					
1 d_1	2 d_2	3 l_1	b	d_3	l_2
13.5 0.53	M 4	20 0.79	11 0.43	11 0.43	8 0.31
13.5 0.53	M 5	20 0.79	11 0.43	11 0.43	10 0.39
16 0.63	M 5	23 0.91	13 0.51	12.5 0.49	10 0.39

Specification

Knob

Plastic, Polyamide (PA)

• Operating temperature up to 176 °F (80 °C)

• Black, matte finish

Threaded spindle

Steel, zinc plated

RoHS

Mini revolving handles EN 595 are used, for example, in connection with small handwheels or cranked handles with low adjustment torque. Finger moldings in Type B provide additional safety against slipping and make operation easier.

Technical Information

Plastic Characteristics

Page

QVX

How to order

1

2

3

4

EN 595-13.5-M4-20-A

1

Handle diameter d_1

2

Thread d_2

3

Length l_1

4

Type