



**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub>	<b>3</b> Length l			d <sub>3</sub>	b	h <sub>1</sub>	h <sub>2</sub>
32 1.26	M 6	10 0.39	16 0.63	20 0.79	11 0.43	13 0.51	14.5 0.57	5.5 0.22
40 1.57	M 8	16 0.63	25 0.98	-	14 0.55	15.5 0.61	17 0.67	7.5 0.30
48 1.89	M 8	16 0.63	25 0.98	-	17 0.67	19 0.75	19 0.75	9 0.35
56 2.20	M 10	20 0.79	30 1.18	-	18.5 0.73	21 0.83	23 0.91	11 0.43

**Specification**

- Wing body  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 266 °F (130 °C)  
- Black, matte finish
- Threaded stud  
Steel, zinc plated, blue passivated finish
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

**On request**

- AISI 303 stainless steel threaded stud

**Information**

EN 531.1 wing screws offer an extended hub for better surface contact and a comfortable grip for quick two finger clamping applications.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- *Wing Screws EN 531* → page 666
- *Wing Screws EN 633* → page 663
- *Small Wing Screws EN 639* → [www.jwwinco.com](http://www.jwwinco.com)

How to order <b>EN 531.1-56-M10-20</b>	<b>1</b>	Handle diameter d <sub>1</sub>
	<b>2</b>	Thread d <sub>2</sub>
	<b>3</b>	Length l

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

