



3 Type

- A Without cover cap
- B With cover cap

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂ Thread		s H9 Square		d ₃	d ₄ -0.5	h ₁	h ₂	l ₁	l ₂	l ₃ +0.5		
32 1.26	M 5	M 6	V 5	V 6	-	-	17 0.67	11 0.43	17 0.67	1 0.04	8 0.31	13.5 0.53	6.5 0.26
40 1.57	M 6	M 8	V 6	-	-	-	17 0.67	13 0.51	17 0.67	1 0.04	10 0.39	14.5 0.57	9.5 0.37
50 1.97	M 8	M 10	V 6	V 7	-	-	19 0.75	16 0.63	20 0.79	1.2 0.05	10 0.39	17.5 0.69	9.5 0.37
63 2.48	M 10	M 12	V 6	V 7	V 8	-	22.5 0.89	20 0.79	21.5 0.85	1.3 0.05	10 0.39	19 0.75	9.5 0.37
74 2.91	M 10	M 12	V 7	V 8	V 9	V 10	26.5 1.04	20 0.79	24.5 0.96	2 0.08	15 0.59	21 0.83	13.5 0.53
95 3.74	M 16	-	V 8	V 10	-	-	32 1.26	18 0.71	29.5 1.16	4.5 0.18	15 0.59	26.5 1.04	13.5 0.53

Specification

- Five-lobed knob
Plastic
Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 266 °F (130 °C)
 - Black, matte finish
- Color of the color cap (only type B)

●	-
●	DOR
●	DGR
●	DGB
●	DBL
●	DRT
●	DGN
- Tapped / square insert
Brass
- RoHS compliant

Information

These EN 5331 knobs are characterized by their 5 lobes and recessed grips. They not only give them an attractive design, but their shape also allows a high torque to be achieved.

How to order (Black cover cap)	1 Handle diameter d ₁
EN 5331-63-M10-A	2 Thread d ₂ (Square s)
	3 Type

How to order (Colored cover cap)	1 Handle diameter d ₁
EN 5331-74-M12-B-DRT	2 Thread d ₂ (Square s)
	3 Type
	4 Color of the cover cap