



Inch table

Dimensions in: inches - millimeters

l ₁	d ₁ Thread			d ₂ +0.001 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
	10 x 32	10 x 24	1/4 x 20	B 1/4	-							
1.73 44	10 x 32	10 x 24	1/4 x 20	B 1/4	-	0.39 10	0.57 14.5	0.96 24.5	0.14 3.5	1.18 30	0.14 3.5	0.31 8
2.48 63	1/4 x 20	5/16 x 18	-	B 5/16	-	0.53 13.5	0.71 18	1.22 31	0.14 3.5	1.50 38	0.16 4	0.39 10
3.07 78	5/16 x 18	3/8 x 16	-	B 5/16	B 3/8	0.63 16	0.85 21.5	1.42 36	0.14 3.5	1.81 46	0.16 4	0.55 14
3.74 95	3/8 x 16	1/2 x 13	-	B 1/2	-	0.75 19	0.98 25	1.69 43	0.20 5	2.20 56	0.16 4	0.67 17

Metric table

Dimensions in: millimeters - inches

l ₁	d ₁ Thread			d ₂ H7 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
	M 4	M 5	M 6	B 5	B 6							
44 1.73	M 4	M 5	M 6	B 5	B 6	10 0.39	14.5 0.57	24.5 0.96	3.5 0.14	30 1.18	3.5 0.14	8 0.31
63 2.48	M 6	M 8	-	B 8	-	13.5 0.53	18 0.71	31 1.22	3.5 0.14	38 1.50	4 0.16	10 0.39
78 3.07	M 8	M 10	M 12	B 8	B 10	16 0.63	21.5 0.85	36 1.42	3.5 0.14	46 1.81	4 0.16	14 0.55
95 3.74	M 10	M 12	-	B 12	-	19 0.75	25 0.98	43 1.69	5 0.20	56 2.20	4 0.16	17 0.67

Specification

- Lever body
Zinc die-cast
- Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Orange, RAL 2004, textured finish **● OS**
 - Red, RAL 3000, textured finish **● RS**
 - Silver, RAL 9006, textured finish **● SR**
- Tapped insert / retaining screw
Steel, blackened finish
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

Information

EN 602 adjustable levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

The slightly arched shape of the lever gives the operator a comfortable and safe grip and makes the design more elegant.

see also...

- Product Family Ergostyle® → page 18
- Adjustable Levers EN 602.1 (Zinc Die-Cast, with Stainless Steel Insert) → page 487

On request

- Special threads or bores

How to order (Inch)	1 Lever length l ₁
EN 602-95-3/8X16-OS	2 Thread d ₁
	3 Color

How to order (Metric)	1 Lever length l ₁
EN 602-63-M6-RS	2 Thread d ₁
	3 Color