



ELESA original design 1.280 p

Metric table

Dimensions in: millimeters - inches

¹ d_1	² d_2 Thread	d_3	l_1	l_2
18 .71	M 6	15 .59	40 1.57	16 .63
21 .83	M 8	17 .67	50 1.97	16 .63
23 .91	M 10	19 .75	65 2.56	16 .63
26 1.02	M 10	21 .83	80 3.15	16 .63
28 1.10	M 12	22 .87	90 3.54	16 .63
31 1.22	M 12	25 .98	102 4.02	16 .63

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, glossy finish
- Spindle
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

EN 539 fixed cylindrical handles can equally well be used to replace ball knobs on operating / gear lever handles. In that case the operating end of the lever handle will need to have a tapped hole for mounting the EN 539 fixed cylindrical handle.

The threaded spindle is deeply embedded in the handle which greatly increases the strength of the plastic body.

see also...

- Revolving Handles GN 598

How to order ¹ ² EN 539-21-M8	1 Handle diameter d_1
	2 Thread d_2

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4