



ELESA original design IF / IFF

4 Type

- A With hand guard, one side
- B With hand guard, both sides

Metric table

1 d ₁	2 d ₂ Thread	3 l ₂	d ₃	d ₄	l ₁	l ₃	l ₄	t
30 1.18	M 8	20 .79	64 2.52	46 1.81	112 4.41	4 .16	4 .16	20 .79
30 1.18	M 10	20 .79	64 2.52	46 1.81	112 4.41	4 .16	4 .16	18 .71

Dimensions in: millimeters - inches

Specification

- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black, matte finish
- Tapped insert
Brass
- Threaded stud
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

EN 539.2 cylindrical handles are used as handles for electrical tools such as angle grinders, percussion drills etc. Their special feature is the hand guard on one or both sides.

see also...

- Fixed Cylindrical Handles EN 539
- Cylindrical Handles EN 519 (with Molded-In Thread)

How to order (Tapped type) EN 539.2-30-M8-A	1 Handle diameter d ₁
	2 Thread d ₂
	3 Type

How to order (Threaded stud) EN 539.2-30-M8-20-A	1 Handle diameter d ₁
	2 Thread d ₂
	3 Thread length l ₂
	4 Type