




Specification	
Lever body	
Plastic, Polyamide (PA)	
• Glass fiber reinforced	
• Operating temperature	
-22 °F to +266 °F (-30 °C to +130 °C)	
• Black-gray, matte finish, similar to RAL 7021	
Threaded stud	
Plastic, Polyamide (PA)	
• Glass fiber reinforced	
• Black	
• Threaded stud	
Steel zinc plated, blue passivated finish	
Push button	
Plastic, Polyamide (PA)	
• Black-gray, RAL 7021, shiny finish	● DSG
• Orange, RAL 2004, shiny finish	● DOR
• Gray, RAL 7035, shiny finish	● DGR
• Yellow, RAL 1021, shiny finish	● DGB
• Blue, RAL 5024, shiny finish	● DBL
• Red, RAL 3000, shiny finish	● DRT
• Green, RAL 6017, shiny finish	● DGN

RoHS

The slightly arched ergonomic shape of the adjustable levers EN 603 gives the operator a comfortable and safe grip, while the thumb rests naturally on the push button.

These levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the mating serrations of the lever and the insert automatically re-engage via a spring and push button that holds the assembly together.

Resistant to solvents, oils, grease and other chemical agents.

see also...	Page
EN 603.1 Adjustable Levers	
(with Stainless Steel Threaded Stud, with Push Button)	QVX
EN 600 Straight Adjustable Levers (with Push Button)	QVX
Technical Information	
Product Family Ergostyle®	QVX
Strength Values of Screws	QVX
Plastic Characteristics	QVX

How to order (Inch)	
1	Lever length l ₁
2	Thread d ₁
3	Thread length l ₂
4	Color of the push button
EN 603-1.73-10X32-0.50-DOR	
How to order (Metric)	
1	Lever length l ₁
2	Thread d ₁
3	Thread length l ₂
4	Color of the push button
EN 603-63-M8-20-DOR	

Inch table

Dimensions in: inches / millimeters										
1 l₁	2 d₁	3 l₂			d₂	d₃	h₁	h₂	h₃	h₄ Stroke
1.73 43.9	10 x 24	0.75 19.1	-	-	0.47 11.9	0.61 15.5	1.16 29.5	0.24 6.1	1.28 32.5	0.14 3.6
1.73 43.9	10 x 32	0.50 12.7	0.75 19.1	-	0.47 11.9	0.61 15.5	1.16 29.5	0.24 6.1	1.28 32.5	0.14 3.6
1.73 43.9	1/4 x 20	0.75 19.1	1.00 25.4	-	0.47 11.9	0.61 15.5	1.16 29.5	0.24 6.1	1.28 32.5	0.14 3.6
2.48 63	5/16 x 18	0.75 19.1	1.00 25.4	1.25 31.8	0.59 15	0.75 19.1	1.48 37.6	0.31 7.9	1.69 42.9	0.16 4.1
3.07 78	3/8 x 16	1.00 25.4	1.25 31.8	1.50 38.1	0.75 19.1	0.91 23.1	1.85 47	0.47 11.9	2.13 54.1	0.16 4.1

Metric table

1	2													Dimensions in: millimeters / inches							
l ₁	d ₁			l ₂										d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke		
30 1.18	M 5	-	-	10 0.39	16 0.63	20 0.79	-	-	-	-	-	-	-	12 0.47	15.5 0.61	29.5 1.16	6 0.24	30 1.18	3.5 0.14		
30 1.18	M 6	-	-	10 0.39	16 0.63	20 0.79	25 0.98	30 1.18	40 1.57	-	-	-	-	12 0.47	15.5 0.61	29.5 1.16	6 0.24	30 1.18	3.5 0.14		
44 1.73	M 5	-	-	10 0.39	16 0.63	20 0.79	-	-	-	-	-	-	-	12 0.47	15.5 0.61	29.5 1.16	6 0.24	32.5 1.28	3.5 0.14		
44 1.73	M 6	-	-	10 0.39	16 0.63	20 0.79	25 0.98	30 1.18	40 1.57	45 1.77	-	-	-	12 0.47	15.5 0.61	29.5 1.16	6 0.24	32.5 1.28	3.5 0.14		
63 2.48	M 6	-	-	10 0.39	16 0.63	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	50 1.97	-	-	15 0.59	19 0.75	37.5 1.48	8 0.31	43 1.69	4 0.16		
63 2.48	M 8	-	-	16 0.63	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	45 1.77	50 1.97	60 2.36	70 2.76	15 0.59	19 0.75	37.5 1.48	8 0.31	43 1.69	4 0.16		
63 2.48	M 10	-	-	20 0.79	40 1.57	50 1.97	60 2.36	-	-	-	-	-	-	15 0.59	19 0.75	37.5 1.48	8 0.31	43 1.69	4 0.16		
78 3.07	M 8	-	-	20 0.79	25 0.98	30 1.18	40 1.57	45 1.77	50 1.97	55 2.17	60 2.36	70 2.76	-	19 0.75	24.5 0.96	47 1.85	12 0.47	54 2.13	4 0.16		
78 3.07	M 10	-	-	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	50 1.97	60 2.36	70 2.76	-	-	19 0.75	24.5 0.96	47 1.85	12 0.47	54 2.13	4 0.16		
78 3.07	M 12	-	-	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	45 1.77	50 1.97	60 2.36	70 2.76	80 3.15	19 0.75	24.5 0.96	47 1.85	12 0.47	54 2.13	4 0.16		
95 3.74	M 12	M 16	-	30 1.18	50 1.97	70 2.76	-	-	-	-	-	-	-	21.5 0.85	26.5 1.04	54.5 2.15	13 0.51	64.5 2.54	4.5 0.18		
108 4.25	M 12	M 14	M 16	30 1.18	50 1.97	70 2.76	-	-	-	-	-	-	-	25 0.98	30 1.18	54.5 2.15	11 0.43	65.5 2.58	4.5 0.18		