



Inch table

Dimensions in: inches - millimeters

Length l	d <sub>2</sub> Thread	h <sub>1</sub>	h <sub>2</sub>	s Square	t min.
2.17 55	1/4 x 20	1.30 33	.87 22	.55 14	.47 12
2.64 67	5/16 x 18	1.46 37	.98 25	.63 16	.63 16
3.15 80	3/8 x 16	1.61 41	1.02 26	.79 20	.63 16

Metric table

Dimensions in: millimeters - inches

Length l	d <sub>1</sub> H7 Bore diameter	d <sub>2</sub> Thread		h <sub>1</sub>	h <sub>2</sub>	s Square	t min.
55 2.17	B 6	M 6	M 8	33 1.30	22 .87	14 .55	12 .47
67 2.64	B 8	M 8	-	37 1.46	25 .98	16 .63	16 .63
80 3.15	B 8	M 8	M 10	41 1.61	26 1.02	20 .79	16 .63

Specification

- Aluminum
  - Powder coated
    - Black, RAL 9005, textured finish
    - Silver, RAL 9006, textured finish
  - Blank
    - Tumbled, flash mark not visible



RoHS compliant

Information

GN 563.2 T-handles can be used as either operating handles or for clamping purposes, providing high clamping force.

T-handles are made by forging and therefore they have a structure with high strength and a smooth surface.

An ELESA original design, produced in metal with permission of ELESA S. p. A.

see also...

- T-Handles EN 563 (Technopolymer Plastic)

On request

- Inch bores

How to order (Inch)	1	Handle length l
	2	Thread d <sub>2</sub>
	3	Finish
GN 563.2-55-1/4X20-BL		

How to order (Metric)	1	Handle length l
	2	Bore diameter d <sub>1</sub> (Thread d <sub>2</sub> )
	3	Finish
GN 563.2-67-B8-SR		

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

