



ELESA original design ERS.



**Inch table**

Dimensions in: inches - millimeters

<sup>1</sup> l <sub>1</sub>	<sup>2</sup> d <sub>1</sub> Thread	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> Stroke	t min.
1.73 44	1/4 x 20	.47 12	.61 15.5	1.14 29	.35 9	1.42 36	.14 3.5	.39 10
2.48 63	5/16 x 18	.59 15	.75 19	1.46 37	.47 12	1.89 48	.16 4	.51 13

**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> l <sub>1</sub>	<sup>2</sup> d <sub>1</sub> Thread	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> Stroke	t min.
44 1.73	M 4 M 5 M 6	12	15.5	29	9	36	3.5	10
63 2.48	M 6 M 8 -	15 .59	19 .75	37 1.46	12 .47	48 1.89	4 .16	13 .51

**Specification**

- Lever body  
 Plastic  
 Technopolymer (Polyamide PA)  
 - Glass fiber reinforced  
 - Temperature resistant up to 266 °F (130 °C)  
 - Black-gray, RAL 7021, matte finish ● **SG**
- Tapped insert / retaining screw  
 Steel, blackened finish
- RoHS compliant

**Information**

EN 604.2 safety adjustable levers like all the products of the Ergostyle® range are renowned for their good style and also their ergonomical shape. The gently arched handle with a reinforced end of the lever gives the operator a good grip.

These safety adjustable levers are used where the inadvertent loosening or readjustment can result in accidents.

If not operated, the lever is not linked to the tapped insert, i.e. the adjustable lever turns freely.

As soon as the lever hub is pushed down, both serrations will engage, allowing the fixture to be released or clamped.

After "releasing", the connection disengages through spring tension.

see also...

- Product Range Ergostyle®
- Safety Adjustable Levers GN 312
- Safety Lobed Knobs GN 5337.3

How to order (Inch) <b>EN 604.2-44-1/4X20-SG</b>	<sup>1</sup> Lever length l <sub>1</sub>
	<sup>2</sup> Thread d <sub>1</sub>
	<sup>3</sup> Color

How to order (Metric) <b>EN 604.2-63-M8-SG</b>	<sup>1</sup> Lever length l <sub>1</sub>
	<sup>2</sup> Thread d <sub>1</sub>
	<sup>3</sup> Color