



SS Stainless Steel

3 Type

A Mounting from the back (tapped blind hole)

Metric table

Dimensions in: millimeters - inches

1 b_1	2 Length $l \pm 0.25$	a	b₂	b₃	b₄	b₅ +1	d Thread	h₁	h₂	r	t min.
20 .79	112 4.41	13 .51	24 .94	32 1.26	50 1.97	13.5 .53	M 6	32 1.26	48 1.89	13 .51	10 .39
20 .79	128 5.04	13 .51	24 .94	32 1.26	50 1.97	13.5 .53	M 6	32 1.26	48 1.89	13 .51	10 .39

Specification

- Stainless steel
European Standard No. 1.4301 (AISI 304),
matte, shot-blasted finish **MT**
- RoHS compliant

Information

GN 565.7 angled cabinet “U” handles are manufactured from a bent stainless steel profile and have excellent stability and ergonomic design. The 35° angled contact surface allows improved access even in tight spaces such as corners.

The manufacturing process allows the production of special lengths in relatively small quantities.

see also...

- Cabinet “U” Handles GN 425.1 (Steel / Stainless Steel / Aluminum, Offset)
- Cabinet “U” Handles GN 426.6 (Stainless Steel, Offset)

On request

- Special lengths
- Various metric size fasteners and kit packaging

How to order

GN 565.7-20-128-A-MT

- 1** Handle width b_1
- 2** Length l
- 3** Type
- 4** Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

