


Metric



RUD®

SS Stainless Steel

Metric table



Dimensions in: millimeters / inches

d ₁	d ₂	d ₃	d ₄	d ₅	h	k ₁	k ₂	Length l	Nominal load (WLL) in metric tons
M 8	16.3 0.64	25 0.98	28 1.10	25 0.98	47 1.85	10 0.39	46 1.81	12 0.47	0.3 t [3 kN]
M 10	16.3 0.64	25 0.98	28 1.10	25 0.98	47 1.85	10 0.39	46 1.81	15 0.59	0.3 t [3 kN]
M 12	18 0.71	30 1.18	32 1.26	30 1.18	57 2.24	12 0.47	56 2.20	18 0.71	0.5 t [5 kN]
M 16	22 0.87	36 1.42	38 1.50	35 1.38	66 2.60	14 0.55	65 2.56	24 0.94	1.0 t [10 kN]
M 20	27.5 1.08	43 1.69	47 1.85	40 1.57	77 3.03	16 0.63	74 2.91	30 1.18	2.0 t [20 kN]
M 24	33 1.30	51 2.01	56 2.20	48 1.89	94 3.70	19 0.75	92 3.62	35 1.38	2.5 t [25 kN]

Specification

Ring

- Stainless steel AISI 318LN
- Forged
- 100% electromagnetic tensile tested according to EN 1677
- Plain finish

Threaded socket head bolt

Stainless steel AISI 318LN

RoHS

The bolt of safety swivel lifting eye bolts GN 581.5 is captively mounted in the ring housing, yet rotates freely. This allows the direction of the load to be adjusted and prevents unintentional loosening or overtightening (as it is possible with DIN 580 lifting eye bolts).

These lifting eye bolts offer a high load carrying capacity and are tested to meet high safety standards in all load directions (safety factor 4).

The nominal values for load capacity in the table are for the most extreme loading conditions listed, and are also clearly marked on the ring.

Lifting eye bolts GN 581.5 comply with Machinery Directive 2006/42/EG and are BG tested.

The integrated RFID transponder clearly marks and identifies the lifting point, e.g. during the prescribed regular inspection.

The hex socket bolt cannot be removed from the ring.

see also...

GN 581 Safety Swivel Lifting Eye Bolts (Steel)

Page

QVX

Technical Information

Stainless Steel Characteristics


QVX

How to order

GN 581.5-M24

1 Thread d₁

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10



Dimensions in: metric tons

d_1	F_1 max. in t	F_2 max. in t
M 8	0.7 [0.14]	0.3
M 10	0.7 [0.23]	0.3
M 12	1.2 [0.34]	0.5
M 16	2.4 [0.7]	1
M 20	3.6 [1.2]	2
M 24	5.2 [1.8]	2.5

Safety instructions

The loads in brackets refer to the load capacity of the corresponding DIN 580 lifting eye bolt. If this value is not indicated, the use of lifting eye bolts DIN 580 is not permitted!

The screw-on surface of the lifting eye bolts GN 581.5 must be plane and at a right angle to the threaded hole; the countersunk must be \leq the nominal diameter of the thread.

When screwed in, the collar of the bolt must fit firmly (do not use washers) and the ring housing must rotate freely by 360°.

Before applying the load, turn the lifting eye bolt in the direction of the load. The lifting eye bolt is not suitable for rotary movements under load.

The specified load values apply to a minimum screw-in length of $1.5 \times$ nominal thread diameter in stainless steel with a minimum tensile strength of 37 kp/mm², at an operating temperature of -40 °F to +536 °F (-40 °C to +280 °C). Load bearing capacity under different conditions on request.

The operating instruction contains further guidelines and is included with every eye bolt (see also at jwwinco.com/en-us/service).