


Calculation drilling distance m

l <sub>1</sub>	m
117	0,044 x D + 81,5
150	0,056 x D + 102,8



ELESA original design EBP.FLX



**2** Type

**B** Mounting from the operator's side

**Metric table**

**1**

Dimensions in: millimeters - inches

l <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	l <sub>3</sub>	s	t
117 ±0.5 4.61 ±0.02	26 1.02	8.5 .33	39 1.54	18 .71	143 5.63	91 3.58	9 .35	8.5 .33
150 ±1 5.91 ±0.04	28 1.10	8.5 .33	45 1.77	18 .71	178 7.01	122 4.80	10 .39	14 .55

**Specification**

**3**

- Plastic  
Technopolymer  
(Polypropylene PP with Elastomer TPE)  
- Temperature resistant up to 176 °F (80 °C)  
- Black-gray, similar to RAL 7021, matte finish
- Inserts  
Brass
- Color of the cover caps (matte finish):  
Black-gray, RAL 7021      ● **DSG**  
Orange, RAL 2004        ● **DOR**  
Gray, RAL 7035            ● **DGR**  
Yellow, RAL 1021        ● **DGB**  
Blue, RAL 5024           ● **DBL**  
Red, RAL 3000            ● **DRT**
- RoHS compliant

**Information**

EN 628.3 Ergostyle® bridge handles are manufactured out of a flexible plastic material. They were developed for use on arched surfaces (see above illustration).  
These flexible handles can be used on curved surfaces with diameters from Ø 300 mm up to Ø 600 mm. For Ø bigger than 600 mm, the standard version EN 628 can be used.  
Cover caps are supplied but not assembled (press-fit, removable with screwdriver).  
*see also...*  
• *Product Range Ergostyle®*  
• *Flexible Ergostyle® Bridge Handles EN 628.3*  
(Mounting from the Back or from the Operator's Side)

**On request**

- Various metric size fasteners and kit packaging

<p>How to order</p> <p><b>EN 628.3-150-B-DSG</b></p>	<b>1</b>	Length l <sub>1</sub>
	<b>2</b>	Type
	<b>3</b>	Color of the cover cap