



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches												
1	2	3			4							
d ₁	d ₂ Thread	l ₁			d ₃	d ₄	d ₅ +0.05	h ₁	h ₂	l ₂	l ₃	l ₄
32 1.26	M 6	25 .98	35 1.38	45 1.77	15 .59	14 .55	4.5 .18	20 .79	10 .39	5.1 .20	3.6 .14	7.6 .30
40 1.57	M 8	30 1.18	40 1.57	50 1.97	18 .71	18 .71	6.1 .24	25 .98	13 .51	6.2 .24	4.2 .17	9.2 .36
40 1.57	M 8	30 1.18	40 1.57	50 1.97	21 .83	18 .71	6.1 .24	25 .98	13 .51	6.2 .24	5 .20	10 .39
40 1.57	M 8	30 1.18	40 1.57	50 1.97	25 .98	18 .71	6.1 .24	25 .98	13 .51	6.2 .24	5.5 .22	10.5 .41
40 1.57	M 8	30 1.18	40 1.57	50 1.97	32 1.26	18 .71	6.1 .24	25 .98	13 .51	6.2 .24	6 .24	11 .43
40 1.57	M 8	30 1.18	40 1.57	50 1.97	40 1.57	18 .71	6.1 .24	25 .98	13 .51	6.2 .24	8 .31	13 .51
50 1.97	M 10	35 1.38	45 1.77	55 2.17	21 .83	22 .87	7.8 .31	32 1.26	17 .67	7.3 .29	4.3 .17	10 .39
50 1.97	M 10	35 1.38	45 1.77	55 2.17	25 .98	22 .87	7.8 .31	32 1.26	17 .67	7.3 .29	4.6 .18	10.5 .41
50 1.97	M 10	35 1.38	45 1.77	55 2.17	32 1.26	22 .87	7.8 .31	32 1.26	17 .67	7.3 .29	5 .20	11 .43
50 1.97	M 10	35 1.38	45 1.77	55 2.17	40 1.57	22 .87	7.8 .31	32 1.26	17 .67	7.3 .29	7 .28	13 .51

Specification

- Star knob DIN 6336
Plastic
Technopolymer (Polyamide PA)
Black, matte finish
- Threaded stud
Stainless steel
European Standard No. 1.4567 (AISI 304 Cu)
- Thrust pad GN 631
Plastic
Technopolymer (Polyacetal POM)
- Temperature resistant up to 176 °F (80 °C)
- Black, matte finish
- RoHS compliant

Information

GN 6336.11 and GN 6336.12 star knobs with stainless steel threaded stud have a ball end whose diameter is smaller than the core diameter of the thread.

These components are an excellent choice for corrosion-free applications.

The swivel thrust pad is easily clipped on and taken off. Thrust pads are supplied unmounted.

see also...

- Hollow Knurled Knobs GN 421.12 (with Swivel Thrust Pad)
- Star Knobs GN 6336.11 / GN 6336.12 with Loss Protection GN 111.7

How to order (With ball end)	1	Handle diameter d ₁
GN 6336.11-40-M8-50	2	Thread d ₂
	3	Length l ₁

How to order (With swivel thrust pad)	1	Handle diameter d ₁
GN 6336.12-50-M10-45-25	2	Thread d ₂
	3	Length l ₁
	4	Thrust pad diameter d ₃