



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂ Thread	Length l ≈								d ₄	h ₁	h ₂	h ₃
		10	15	20	-	-	-	-	-				
25 .98	M 5	.39	.59	.79	-	-	-	-	-	10 .39	16 .63	8 .31	6 .24
32 1.26	M 6	.63	.79	.98	1.18	1.38	1.77	-	-	12 .47	20 .79	10 .39	8.5 .33
40 1.57	M 8	.63	.79	.98	1.18	1.38	1.57	1.77	2.17	14 .55	26 1.02	13 .51	10 .39
50 1.97	M 10	.98	1.18	1.38	1.77	2.17	-	-	-	18 .71	32 1.26	17 .67	10 .39
63 2.48	M 12	1.18	1.38	1.57	1.97	2.36	-	-	-	20 .79	40 1.57	21 .83	14 .55

Specification

- Star knob
Plastic
Technopolymer (Polyamide PA)
- Shock-resistant
- Black, matte finish
- GN 6336.4**
Threaded stud
Steel, zinc plated, blue passivated finish
- GN 6336.5**
Threaded stud
Stainless steel
European Standard No. 1.4305 (AISI 303)
- RoHS compliant

1

TE

Information

GN 6336.4 star knobs with protruding hub and threaded stud increase the range of application. Due to the protruding hub and threaded stud being a solid one-piece unit, a strong and secure contact to the clamping surface is created.

see also...

- Star Knobs GN 6336.4 (without Protruding Hub, with Steel Threaded Stud)
- Star Knobs GN 6336.5 (Stainless Steel, without Protruding Hub, with Stainless Steel Threaded Stud)

On request

- Special shorter than listed stud lengths and various stud tips

How to order (Steel threaded stud)	1 Material
<p>1 2 3 4</p> <p>GN 6336.4-TE-50-M10-30</p>	2 Handle diameter d ₁
	3 Thread d ₂
	4 Length l

How to order (Stainless steel threaded stud)	1 Material
<p>1 2 3 4</p> <p>GN 6336.5-TE-40-M8-16</p>	2 Handle diameter d ₁
	3 Thread d ₂
	4 Length l