



SS Stainless Steel

4 Type

- K With tapped insert
- D With tapped through bore

Specification

<ul style="list-style-type: none"> • Plastic Duroplast (Phenolic PF), black, shiny finish 	KU
<ul style="list-style-type: none"> • Tapped insert - Steel, zinc plated, blue passivated finish (standard) - Brass 	MS
<ul style="list-style-type: none"> • Plastic Technopolymer (Polyamide PA) - Black, matte finish - Shock-resistant 	KT
<ul style="list-style-type: none"> • Tapped insert - Steel, zinc plated, blue passivated finish (standard) - Stainless steel 	NI
<ul style="list-style-type: none"> • RoHS compliant 	

Information

DIN 6336 star knobs are an economical choice yet offer top quality and ergonomic styling. The version with stainless steel insert is suitable for certain non-corrosive environment applications.

see also...

- Star Knobs DIN 6336 (Cast Iron / Stainless Steel / Aluminum)
- Star Knobs GN 6336.1 (Duroplast, with Protruding Hub)
- Star Knobs GN 6336.2 (Technopolymer, with Protruding Hub)

How to order (Inch, Duroplast, steel insert)	1 Material
1 2 3 4	2 Handle diameter d_1
DIN 6336-KU-50-1/4X20-K	3 Thread d_2
	4 Type

How to order (Metric, Technopolymer, stainless steel insert)	1 Material
1 2 3 4 5	2 Handle diameter d_1
DIN 6336-KT-50-M10-K-NI	3 Thread d_2
	4 Type
	5 Bush

Inch table

Dimensions in: inches - millimeters

d ₁	d ₂			d ₃	h ₁	h ₂	t ₁ min.	t ₂
	Steel insert Plastic KU Type K	Plastic KT Type K	Plastic KT Type D					
.98 25	-	10 x 32	-	.47 12	.63 16	.31 8	.37 9.5	-
1.26 32	-	1/4 x 20	-	.55 14	.79 20	.39 10	.47 12	-
1.57 40	-	5/16 x 18	-	.71 18	.98 25	.51 13	.55 14	.51 13
1.97 50	1/4 x 20	3/8 x 16	-	.87 22	1.26 32	.67 17	.71 18	.67 17
2.48 63	5/16 x 18	1/2 x 13	-	1.02 26	1.57 40	.83 21	.87 22	.83 21
3.15 80	3/8 x 16	-	-	1.38 35	1.97 50	.98 25	1.18 30	-

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂			Brass insert MS Plastic KU Type K	Stainless steel insert NI Plastic KT Type K	d ₃	h ₁	h ₂	t ₁ min.	t ₂
	Steel insert Plastic KU Type K	Plastic KT Type K	Plastic KT Type D							
20 .79	-	-	-	M 4	-	10 .39	13 .51	7 .28	6.5 .26	-
25 .98	M 5	M 5	-	M 5	-	12 .47	16 .63	8 .31	9.5 .37	-
32 1.26	-	M 4	-	-	-	14 .55	20 .79	10 .39	6.5 .26	-
32 1.26	-	M 5	-	-	M 5	14 .55	20 .79	10 .39	9.5 .37	-
32 1.26	M 6	M 6	M 6	M 6	M 6	14 .55	20 .79	10 .39	12 .47	10.5 .41
40 1.57	M 6	M 6	-	M 6	M 6	18 .71	25 .98	13 .51	12 .47	-
40 1.57	M 8	M 8	M 8	M 8	M 8	18 .71	25 .98	13 .51	14 .55	13 .51
50 1.97	M 8	M 8	M 8	M 8	M 8	22 .87	32 1.26	17 .67	14 .55	16 .63
50 1.97	M 10	M 10	M 10	M 10	M 10	22 .87	32 1.26	17 .67	18 .71	16 .63
63 2.48	M 10	M 10	-	M 10	M 10	26 1.02	40 1.57	21 .83	18 .71	-
63 2.48	M 12	M 12	M 12	M 12	M 12	26 1.02	40 1.57	21 .83	22 .87	20 .79
80 3.15	M 12	M 12	-	M 12	M 12	35 1.38	50 1.97	25 .98	22 .87	-
80 3.15	M 16	M 16	-	M 16	M 16	35 1.38	50 1.97	25 .98	30 1.18	-

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

