




Specification

4

Lever body

Zinc die-cast

Powder coated

• Black, RAL 9005, textured finish

• Orange, RAL 2004, textured finish

• Red, RAL 3000, textured finish

• Silver, RAL 9006, textured finish

● SW

● OS

● RS

● SR

Threaded stud / Retaining screw

Steel, blackened finish

Property class 5.8

RoHS

On request

• Special stud lengths

Adjustable levers EN 602 have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged. Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage. The slightly arched shape of the lever gives the operator a comfortable and safe grip and makes the design more elegant.

see also...	Page
EN 602.1 Adjustable Levers (Zinc Die-Cast, Stainless Steel Threaded Stud)	QVX
EN 604 Adjustable Levers (Plastic, Steel Threaded Stud)	QVX
Technical Information	
Strength Values of Screws	QVX
Product Family Ergostyle®	QVX

www.jwwinco.com | 1-800-877-8351

 WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov

1

Inch table

Dimensions in: inches / millimeters																
¹ l ₁	² d ₁	³ l ₂									d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke
1.73 44	10 x 32	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.14 3.5	1.18 30	0.14 3.5
1.73 44	10 x 24	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.14 3.5	1.18 30	0.14 3.5
1.73 44	1/4 x 20	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	0.39 10	0.57 14.5	0.96 24.5	0.14 3.5	1.18 30	0.14 3.5
2.48 63	1/4 x 20	0.47 12	0.63 16	0.79 20	0.98 25	-	-	-	-	-	0.53 13.5	0.71 18	1.22 31	0.14 3.5	1.50 38	0.16 4
2.48 63	5/16 x 18	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.53 13.5	0.71 18	1.22 31	0.14 3.5	1.50 38	0.16 4
2.48 63	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.53 13.5	0.71 18	1.22 31	0.14 3.5	1.50 38	0.16 4
3.07 78	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.63 16	0.85 21.5	1.42 36	0.14 3.5	1.81 46	0.16 4
3.07 78	1/2 x 13	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	-	-	0.63 16	0.85 21.5	1.42 36	0.14 3.5	1.81 46	0.16 4
3.74 95	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.75 19	0.98 25	1.69 43	0.20 5	2.20 56	0.16 4
3.74 95	1/2 x 13	0.63 16	0.79 20	0.98 25	1.26 32	1.38 35	1.57 40	1.77 45	1.97 50	2.48 63	0.75 19	0.98 25	1.69 43	0.20 5	2.20 56	0.16 4

Metric table

1	2	3	Dimensions in: millimeters / inches													
l ₁	d ₁		l ₂								d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke
44 1.73	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	14.5 0.57	24.5 0.96	3.5 0.14	30 1.18	3.5 0.14
44 1.73	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	10 0.39	14.5 0.57	24.5 0.96	3.5 0.14	30 1.18	3.5 0.14
63 2.48	M 6	M 8	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	18 0.71	31 1.22	3.5 0.14	38 1.50	4 0.16
63 2.48	M 10	-	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	13.5 0.53	18 0.71	31 1.22	3.5 0.14	38 1.50	4 0.16
78 3.07	M 8	M 10	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 0.63	21.5 0.85	36 1.42	3.5 0.14	46 1.81	4 0.16
78 3.07	M 12	-	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	16 0.63	21.5 0.85	36 1.42	3.5 0.14	46 1.81	4 0.16
95 3.74	M 10	M 12	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	19 0.75	25 0.98	43 1.69	5 0.20	56 2.20	4 0.16
95 3.74	M 16	-	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	19 0.75	25 0.98	43 1.69	5 0.20	56 2.20	4 0.16