



- 4 Type**
- M** Straight lever
 - N** Angled lever

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Thread	3 l ₁						d ₃	d ₄	h ₁	h ₂	h ₃ ≈	l ₂	l ₃ ≈
20 0.79	M 8	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	20 0.79	25 0.98	8 0.31	46 1.81	74 2.91	70 2.76
25 0.98	M 10	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	16 0.63	25 0.98	29 1.14	8 0.31	58 2.28	93 3.66	87 3.43
28 1.10	M 12	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	19 0.75	30 1.18	33.5 1.32	10.5 0.41	70.5 2.78	116 4.57	109 4.29

Specification

- Body / lever / insert / knurled screw
Steel, blackened finish
- Threaded stud
Property class 5.8
- Ball knob DIN 319 → page 55
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- Strength Values of Screws → page 2127
- RoHS compliant

Information

GN 6337.3 adjustable ball levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected with the lever via serrations in the ball bore that can be disengaged.

Pushing the lever downwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

If a rotation of 360° is not possible, the insert can be screwed-in (after the lever is disengaged) via a slot in the knurled screw.

<p>How to order</p> <p>GN6337.3-28-M12-50-N</p>	1 Diameter d ₁
	2 Thread d ₂
	3 Thread length l ₁
	4 Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4