



SS Stainless Steel

4 Type

- A** With cylindrical bore
- B** With bore for countersunk screw

Metric table

Dimensions in: millimeters - inches

2 d_1 ^{+0.5} / _{+0.2}	3 d_2	d_3 Type B	s
4 .16	10 .39	13 .51	2.5 .10
5 .20	13 .51	16 .63	3 .12
6 .24	15 .59	20 .79	4 .16
8 .31	20 .79	26 1.02	5 .20
10 .39	25 .98	32 1.26	6.5 .26
12 .47	30 1.18	40 1.57	7.5 .30

Specification

- Steel, turned **ST**
- Blackened finish **BT**
- Zinc plated, blue passivated finish **ZB**
- Stainless steel, turned **NI**
- European Standard No. 1.4305 (AISI 303)
- Matte shot-blasted finish **MT**
- RoHS compliant

Information

GN 6341 washers are mainly used in mechanical machine and jig construction when DIN 125, DIN 9021 and DIN 6340 washers do not meet the requirements.

In particular, type B for countersunk screws is ideal for solid screw connections with a low construction height.

see also...

- Heavy Duty Washers GN 6339
- Countersunk Washers GN 184 / GN 184.5
- Heavy Duty Flat Washers DIN 6340

How to order

GN6341-ST-8-26-B-ZB

1	Material
2	Inner diameter d_1
3	Outer diameter d_2
4	Type
5	Finish