



Inch table

Dimensions in: inches - millimeters

1		2		3											
l_1	d_1 Thread	l_2		d_2		d_3	h_1	h_2	h_3	h_4 Stroke					
2.48 63	5/16 x 18	0.79 20	1.26 32	1.57 40	2.48 63	-	0.53 13.5	0.75 19	1.22 31	0.14 3.5	1.52 38.5	0.16 4			
3.07 78	3/8 x 16	0.98 25	1.26 32	1.57 40	1.97 50	2.48 63	0.63 16	0.91 23	1.42 36	0.14 3.5	1.83 46.5	0.16 4			

Metric table

Dimensions in: millimeters - inches

1		2		3											
l_1	d_1 Thread	l_2		d_2		d_3	h_1	h_2	h_3	h_4 Stroke					
63 2.48	M 6 M 8	-	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	19 0.75	31 1.22	3.5 0.14	38.5 1.52	0.16 0.16
78 3.07	M 8 M 10 M 12		20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 0.63	23 0.91	36 1.42	3.5 0.14	46.5 1.83	4 0.16

Specification

- Lever body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black-gray, RAL 7021, matte finish **● SGA**
- White, RAL 9016, matte finish **○ WSA**
- Serrated inlay
Zinc die-cast
- Threaded stud / retaining screw
Stainless steel AISI 303
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

EN 604.1 adjustable levers are manufactured from an antibacterial plastic. Adding a silver-based substance has created a natural active agent that helps to prevent the growth of bacteria. Even after repeated cleaning with soap or solvent, the antibacterial effect of this additive will not diminish. Sterilizing at temperatures up to 266 °F (130 °C) will also have no effect on the antibacterial property.

With these properties, operating parts made of this plastic are the perfect choice for use in medical engineering, in the food and the pharmaceutical industry, and in general wherever hygiene is of great importance.

see also...

- Product Family Sanline → page 2131
- Product Family Ergostyle® → page 18
- Adjustable Levers EN 604 (Plastic, with Steel Threaded Stud) → page 496
- Adjustable Levers EN 602.1 (Zinc Die-Cast, with Stainless Steel Threaded Stud) → page 490
- Adjustable Levers EN 604.1 (Plastic, with Stainless Steel Threaded Stud) → page 498

How to order (Inch)	1 Lever length l_1
	2 Thread d_1
EN 604.1-63-5/16X18-20-WSA	3 Thread length l_2
	4 Color

How to order (Metric)	1 Lever length l_1
	2 Thread d_1
EN 604.1-78-M10-25-SGA	3 Thread length l_2
	4 Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

