



Metric table

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Thread	<b>3</b> Length l				d <sub>3</sub>	b	h <sub>1</sub>	h <sub>2</sub>
32 1.26	M 4	10 0.39	16 0.63	-	-	12 0.47	6 0.24	16.5 0.65	3.5 0.14
32 1.26	M 5	10 0.39	16 0.63	20 0.79	-	12 0.47	6 0.24	16.5 0.65	3.5 0.14
32 1.26	M 6	10 0.39	16 0.63	20 0.79	25 0.98	12 0.47	6 0.24	16.5 0.65	3.5 0.14
40 1.57	M 8	16 0.63	20 0.79	25 0.98	30 1.18	13.5 0.53	6.5 0.26	21 0.83	4.5 0.18

Specification

- Wing body  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 266 °F (130 °C)  
- Black, matte finish
- Threaded stud  
Steel, zinc plated, blue passivated finish
- Plastic Characteristics
- RoHS compliant

Information

The slightly concave indentations on the ends of the EN 639 small wing screws help to position the fingers to apply the maximum force when tightening.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Ergostyle® Wing Screws EN 633
- Wing Screws EN 531
- Wing Screws EN 531.1

How to order <b>EN 639-40-M8-20</b>	<b>1</b>	Handle diameter d <sub>1</sub>
	<b>2</b>	Thread d <sub>2</sub>
	<b>3</b>	Length l