



Inch table

Dimensions in: inches - millimeters

¹ l ₁	² d ₁ Thread		d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
1.73 44	10 x 32	1/4 x 20	0.39 10	0.61 15.5	0.96 24.5	0.14 3.5	1.20 30.5	0.14 3.5	0.31 8
2.48 63	1/4 x 20	5/16 x 18	0.53 13.5	0.75 19	1.22 31	0.14 3.5	1.52 38.5	0.16 4	0.39 10
3.07 78	5/16 x 18	3/8 x 16	0.63 16	0.91 23	1.42 36	0.14 3.5	1.83 46.5	0.16 4	0.55 14
3.74 95	3/8 x 16	1/2 x 13	0.75 19	1.04 26.5	1.69 43	0.20 5	2.22 56.5	0.16 4	0.67 17

Metric table

Dimensions in: millimeters - inches

¹ l ₁	² d ₁ Thread		d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	t min.	
44 1.73	M 4	M 5	M 6	10 0.39	15.5 0.61	24.5 0.96	3.5 0.14	30.5 1.20	3.5 0.14	8 0.31
63 2.48	M 6	M 8	-	13.5 0.53	19 0.75	31 1.22	3.5 0.14	38.5 1.52	4 0.16	10 0.39
78 3.07	M 8	M 10	-	16 0.63	23 0.91	36 1.42	3.5 0.14	46.5 1.83	4 0.16	14 0.55
95 3.74	M 10	M 12	-	19 0.75	26.5 1.04	43 1.69	5 0.20	56.5 2.22	4 0.16	17 0.67

Specification

- Lever body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black-gray, RAL 7021, matte finish ● **SG**
- Serrated inlay
Zinc die-cast
- Tapped insert / retaining screw
Steel, blackened finish
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Lever body
Orange, RAL 2004, matte finish ● **OR**

Information

EN 604 adjustable levers like all the products of the Ergostyle® product family are renowned for their good style and also their ergonomic shape. The gently arched handle with a reinforced end of the lever gives the operator a good grip.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- Product Family Ergostyle® → page 18
- Adjustable Levers EN 602 (Zinc Die-Cast, with Steel Insert) → page 486

How to order (Inch)	¹ Lever length l ₁
² EN 604-78-3/8X16-SG	² Thread d ₁
³	³ Color

How to order (Metric)	¹ Lever length l ₁
² EN 604-44-M6-SG	² Thread d ₁
³	³ Color