



Inch table

Dimensions in: inches - millimeters

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.
0.83* 21	10 x 32	0.49 12.5	0.71 18	0.41 10.5	0.39 10
0.98* 25	1/4 x 20	0.57 14.5	0.89 22.5	0.55 14	0.47 12
1.22* 31	5/16 x 18	0.73 18.5	1.06 27	0.67 17	0.63 16

Metric table

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.
16 0.63	M 3	-	8.5 0.33	8.5 0.33	6 0.24
18 0.71	M 4	-	10.5 0.41	10.5 0.41	6 0.24
21 0.83	M 4	M 5	12.5 0.49	10.5 0.41	10 0.39
25 0.98	M 6	M 8	14.5 0.57	14 0.55	12 0.47
31 1.22	M 6	M 8	18.5 0.73	17 0.67	15 0.59
31 1.22	M 10	-	18.5 0.73	17 0.67	17 0.67
35 1.38	M 6	M 8	20 0.79	17 0.67	15 0.59
35 1.38	M 10	-	20 0.79	17 0.67	17 0.67

\*Only available in black, other colors on request

Specification

- Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 266 °F (130 °C)
- Color (matte finish):
  - SG Black-gray, RAL 7021
  - RT Red, RAL 3000
  - OR Orange, RAL 2004
  - GR Gray, RAL 7035
  - GB Yellow, RAL 1021
  - BL Blue, RAL 5024
  - GN Green, RAL 6017
- Tapped insert  
Brass
- Plastic Characteristics → page 2135
- RoHS compliant

Information

When used as a push-pull button, the thumb rests naturally on the concave front surface, making it easier to grip the EN 676 knurled knob. The slight knurling on the rim of the knob makes tightening or clamping operations easier.  
Resistant to solvents, oils, grease and other chemical agents.

On request

- Knobs with inch thread in other colors

How to order (Inch)	1 Handle diameter d <sub>1</sub>
<sup>1</sup> <sup>2</sup> <sup>3</sup> EN 676-21-10X32-SG	2 Thread d <sub>2</sub>
	3 Color

How to order (Metric)	1 Handle diameter d <sub>1</sub>
<sup>1</sup> <sup>2</sup> <sup>3</sup> EN 676-25-M6-RT	2 Thread d <sub>2</sub>
	3 Color

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4