

GN 612.1


Steel / Stainless Steel

Mounting Blocks

for Indexing Plungers / Cam Action Indexing Plungers



JW WINCO
A Ganter Company



SS Stainless Steel

2 Type

- A Mounting holes parallel to plunger
- B Mounting holes vertical to plunger

Metric table



Dimensions in: millimeters - inches

d ₁ Thread	d ₂	d ₃ Thread	d ₄	d ₅	k ±0.1	l ₁	l ₂ ≈	l ₃	s	t
M 12 x 1.5	32 1.26	M 5	4.5 0.18	12.2 0.48	21 0.83	22 0.87	26.5 1.04	9 0.35	12 0.47	3 0.12
M 16 x 1.5	46 1.81	M 8	5.5 0.22	16.2 0.64	32 1.26	33 1.30	37 1.46	13 0.51	15 0.59	3 0.12
M 20 x 1.5	46 1.81	M 8	5.5 0.22	20.2 0.80	32 1.26	33 1.30	37 1.46	13 0.51	15 0.59	3 0.12

Specification



- Mounting block
 - Steel, blackened finish
 - Stainless steel
- Set screw GN 913.3 with brass tip
- European Standard No. 1.4305 (AISI 303)
- Set screw GN 913.5 with brass tip
- RoHS compliant

Information

GN 612.1 mounting blocks are an accessory that broadens the mounting possibilities for indexing plungers (e.g. GN 817) and GN 612, GN 712 and GN 712.1 cam action indexing plungers.

To position the plunger pin of an indexing plunger or cam action indexing plunger, they can also accommodate GN 412.2 locating bushings.

see also...

- Locating Bushings GN 412.2 / GN 412.4
- Locating Bushings with Tapered Flange GN 412.3 / GN 412.5
- Mounting Blocks GN 412.1 (Zinc Die-Cast)

How to order (Steel)	1 Thread d ₁
GN 612.1-M20x1.5-A	2 Type

How to order (Stainless steel)	1 Thread d ₁
GN 612.1-M16x1.5-B-NI	2 Type
	3 Material

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

