



SS Stainless Steel

3 Type

L Angled

Metric table

Dimensions in: millimeters - inches

m₀	d₁ +0.1 Bore				k	d₂	l₁	l₂	l₃	l₄	l₅	l₆	m	s
8 0.31	B 8	B 12	-	-	14 0.55	3.5 0.14	13 0.51	9.5 0.37	15 0.59	19 0.75	-	-	8 0.31	2 0.08
10 0.39	B 8	B 12	B 18	-	18 0.71	4.5 0.18	14.5 0.57	10.5 0.41	19 0.75	24.5 0.96	29.5 1.16	-	10 0.39	2 0.08
12 0.47	B 8	B 12	B 18	B 30	23 0.91	4.5 0.18	17 0.67	12.5 0.49	19 0.75	24.5 0.96	29.5 1.16	35.5 1.40	12 0.47	2.5 0.10
18 0.71	B 8	B 12	B 18	B 30	30 1.18	5.5 0.22	18.5 0.73	12.5 0.49	24.5 0.96	24.5 0.96	29.5 1.16	35.5 1.40	18 0.71	2.5 0.10

Specification

- Stainless steel, matte shot-blasted finish
European Standard No. 1.4301 (AISI 304)
- RoHS compliant

Information

GN 7062.10 sensor brackets are designed for holding sensors that are attached with two lock nuts. The bores d_2 match the tapped attachment holes of GN 7062.1 / GN 7072.1 shaft collars and facilitate an axial or radial positioning of the sensors.

see also...

- Semi-Split Shaft Collars GN 7062.1 (with Tapped Attachment Holes)
- Split Shaft Collars GN 7072.1 (with Tapped Attachment Holes)

<p>How to order</p> <p>GN 7062.10-B18-30-L</p>	1	Bore d_1
	2	Width k
	3	Type