



- 3** Type
- N** Neutral
 - M** With arrow
 - S** With scale 0...9, 20 graduations

Metric table

Dimensions in: millimeters - *inches*

1 d ₁	2 d ₂ H8 Bore		d ₃ -0.2	d ₄	d ₅ Thread	l ₁	l ₂	l ₃	l ₄	t ₁ min.	t ₂
27 <i>1.06</i>	B 6	-	33.5 <i>1.32</i>	23.5 <i>.93</i>	M 4	25.5 <i>1.00</i>	7.5 <i>0.30</i>	10.5 <i>0.41</i>	12.5 <i>0.49</i>	23.5 <i>0.93</i>	7.5 <i>0.30</i>
34 <i>1.34</i>	B 6	B 8	41 <i>1.61</i>	29.5 <i>1.16</i>	M 5	29.5 <i>1.16</i>	9.5 <i>0.37</i>	13.5 <i>0.53</i>	13 <i>0.51</i>	26.5 <i>1.04</i>	9.5 <i>0.37</i>
42 <i>1.65</i>	B 8	B 10	50 <i>1.97</i>	37.5 <i>1.48</i>	M 5	33.5 <i>1.32</i>	10.5 <i>0.41</i>	15.5 <i>0.61</i>	15 <i>0.59</i>	30.5 <i>1.20</i>	11.5 <i>0.45</i>

Specification

- Aluminum
Anodized finish, natural color
- Scale (Type S) and arrow (Type M)
Laser engraved
- Socket set screw DIN 916
Stainless steel
with internal hex and serrated point
- *ISO Fundamental Tolerances* → page QVX
- **RoHS compliant**

Accessory

- Control knob flanges GN 723.3 are to be ordered separately

On request

- Special graduations
see „How to order Graduations“ → page QVX

Information

- Scale and arrow on the control knobs are clearly marked and easily legible.
- In addition to the standard scale (Type S), they can be supplied with any type of graduation.
- GN 723.4 control knobs can be combined with GN 723.3 control knob flanges, which offer the following advantages:
- They are provided with a reference mark relating to the scale on the control knobs.
 - They give additional support to the control shaft.
 - They can be supplied with end stop pins to limit the angular rotations.
 - The versions with friction ring prevent unexpected movement due to vibration.

Regarding design, numbering position and numbering sequence of the scale please see the layout for scale knobs on the order sheet "How to order Graduations".

see also...

- *Control Knob Flanges GN 723.3 (for GN 723.4)* → page QVX
- *Knurled Control Knobs GN 726.2 (Aluminum)* → page QVX
- *Control Knob Flanges GN 826 (for Adjustable Spindles)* → page QVX

How to order GN 723.4-42-B10-S	1	Outside diameter d ₁
	2	Bore d ₂
	3	Type



GN 723.4 knurled control knob combined with GN 723.3 control knob flange → page QVX

