



ELESA original design M.943

Metric table

| ¹ $l_1 \pm 0.5$ | ² d_1 Thread | ² d_2 Bore | b | h | l_2 | l_3 | s | t min. |
|----------------------------|------------------------------|----------------------------|-------------|--------------|-------------|---------------|-----------|-------------|
| 88 3.46 | M 5 | B 4.5 | 13.5 .53 | 36.5 1.44 | 112 4.41 | 74.5 2.93 | 9 .35 | 10 .39 |
| 120 4.72 | M 5 | B 4.5 | 15 .59 | 42 1.65 | 144 5.67 | 106.5 4.19 | 11 .43 | 10 .39 |

Dimensions in: millimeters - inches

Specification

- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black, matte finish
- Tapped inserts
Brass, molded-in
- RoHS compliant

Information

The dimensions of EN 627 cabinet "U" handles are suitable for 19" rack and enclosure layout. They have been designed for mounting via the threaded inserts or via sheet metal screws with thread size ST 4.8, such as DIN ISO 7049 pan head screws. Maximum recommended tightening torque is 5 Nm. Resistant to solvents, oils, grease and other chemical agents.

see also...

- Cabinet "U" Handles GN 427 (Aluminum, Ellipse Shaped Profile)
- Cabinet "U" Handles GN 427.5 (Stainless Steel, Ellipse Shaped Profile)
- Cabinet "U" Handles GN 425 (Aluminum / Stainless Steel)

On request

- Various metric size fasteners and kit packaging

| | |
|---|-------------------------------------|
| <p>How to order</p> <p>¹ ²</p> <p>EN 627-88-M5</p> | 1 Length l_1 |
| | 2 Thread d_1 (Bore d_2) |