



Application example



Calculation drilling distance m

l_1	m
117	$0,044 \times D + 81,5$
150	$0,056 \times D + 102,8$



ELESA original design EBP.FLX



2 Type

B Mounting from the operator's side

Metric table



Dimensions in: millimeters - inches

l_1	d_2	d_3	h_1	h_2	l_2	l_3	s	t
117 ±0.5 4.61 ±0.02	26 1.02	8.5 .33	39 1.54	18 .71	143 5.63	91 3.58	9 .35	8.5 .33
150 ±1 5.91 ±0.04	28 1.10	8.5 .33	45 1.77	18 .71	178 7.01	122 4.80	10 .39	14 .55

Specification



- Plastic
Technopolymer
(Polypropylene PP with Elastomer TPE)
- Temperature resistant up to 176 °F (80 °C)
- Black-gray, similar to RAL 7021, matte finish
- Inserts
Brass
- Color of the cover caps (matte finish):
Black-gray, RAL 7021 ● DSG
Orange, RAL 2004 ● DOR
Gray, RAL 7035 ● DGR
Yellow, RAL 1021 ● DGB
Blue, RAL 5024 ● DBL
Red, RAL 3000 ● DRT
- RoHS compliant

Information

EN 628.3 Ergostyle® bridge handles are manufactured out of a flexible plastic material. They were developed for use on arched surfaces (see above illustration).

These flexible handles can be used on curved surfaces with diameters from Ø 300 mm up to Ø 600 mm. For Ø bigger than 600 mm, the standard version EN 628 can be used.

Cover caps are supplied but not assembled (press-fit, removable with screwdriver).

see also...

- Product Range Ergostyle®
- Flexible Ergostyle® Bridge Handles EN 628.3
(Mounting from the Back or from the Operator's Side)

On request

- Various metric size fasteners and kit packaging

How to order EN 628.3-150-B-DSG	1	Length l_1
	2	Type
	3	Color of the cover caps