



Metric table

| 1 d_1 | 2 d_2 H8 Bore | | 2 d_3 Collet | d_4 | d_5 | d_6 | d_7 | h_1 | h_2 | h_3 | h_4 | Length l | t |
|----------------|------------------------|------|-----------------------|------------|------------|-------|--------------|------------|------------|-------------|------------|--------------|------------|
| 22 0.87 | B 5 | - | - | 16 0.63 | 14 0.55 | M 4 | 27.5 1.08 | 22 0.87 | 16 0.63 | 4.3 0.17 | 8 0.31 | 12.5 0.49 | - |
| 27 1.06 | B 6 | - | Z 6 | 20 0.79 | 18 0.71 | M 4 | 33.5 1.32 | 26 1.02 | 20 0.79 | 4.3 0.17 | 9 0.35 | 14 0.55 | 14 0.55 |
| 34 1.34 | B 6 | B 8 | Z 8 | 25 0.98 | 23 0.91 | M 5 | 41 1.61 | 30 1.18 | 24 0.94 | 4.2 0.17 | 10 0.39 | 15 0.59 | 17 0.67 |
| 42 1.65 | B 8 | B 10 | Z 10 | 32 1.26 | 30 1.18 | M 5 | 50 1.97 | 34 1.34 | 28 1.10 | 4 0.16 | 11 0.43 | 16 0.63 | 20 0.79 |

Specification

| |
|---|
| Knob Aluminum Black, anodized finish |
| Scale ring <ul style="list-style-type: none">• Plastic, black• Pressed-on• Arrow for type A White, laser engraved• Scale for type S White, laser engraved |
| Cover Plastic, light gray |
| Collet / Hex nut Brass |
| Socket set screw DIN 916 Stainless steel with internal hex and serrated point |
| RoHS |
| On request <ul style="list-style-type: none">• Special graduations (see „How to Order Graduations“) |

The light gray cover makes these control knobs GN 726.2 an aesthetically pleasing choice. The cover is held in place by firmly pushing it into the recess. It can be removed by inserting a screw driver into the slot provided. The collet type provides a simple way of positioning and locking the control knob to the shaft.

Besides the standard scale (Type S) the control knobs can be supplied with any type of graduation.

Other types than the standard scale can be supplied, see order examples on „How to Order Graduations“.

| see also... | Page |
|---|------|
| GN 726.1 Knurled Control Knobs (Aluminum) | QVX |
| GN 723.4 Knurled Control Knobs (Aluminum) | QVX |

| Technical Information | |
|----------------------------|-----|
| How to Order Graduations | QVX |
| ISO Fundamental Tolerances | QVX |

| Accessory | |
|---|-----|
| GN 826 Control Knob Flanges (for Adjustable Spindles) | QVX |

| | |
|--------------|-------------------------------------|
| How to order | 1 Outside diameter d_1 |
| | 2 Collet d_3 (Bore d_2) |
| | 3 Type |
| | 4 Identification no. |

GN 726.2-27-Z6-S-2