



- 2 Type**
- A** Mounting from the operator's side (for identification no. 2 with four countersunk sealing screws)
 - C** Mounting from the back
- 3 Identification no.**
- 1** Without seal
 - 2** With seal

Metric table

1

Dimensions in: millimeters - inches

l_1	h_1	h_2	l_2	l_3	l_4	l_5	$l_6 + 1$	$l_7 + 1$	m_1	m_2
127	80	43	72	25	3.5	22.5	60	88	100	53
5.00	3.15	1.69	2.83	0.98	0.14	0.89	2.36	3.46	3.94	2.09
155	80	43	99	25	3.5	22.5	60	115	128	53
6.10	3.15	1.69	3.90	0.98	0.14	0.89	2.36	4.53	5.04	2.09

Specification

4

- Zinc die-cast
Powder coated
Black, RAL 9005, textured finish **● SW**
Silver, RAL 9006, textured finish **● SR**
- Housing seal (Identification no. 2)
Black NBR rubber, glued
- Countersunk sealing screws DIN 7991 M5x16 (Type A, Identification no. 2)
 - Stainless steel A2
 - Polyamide coating on head
- Threaded studs (Type C)
 - Stainless steel A2
 - Molded-in
- Protection class IP 66
- RoHS compliant

Information

GN 7330 gripping trays can be easily and quickly installed from the front using countersunk screws or from the back with threaded studs.

Gripping trays with housing seal (identification no. 2) prevent the penetration of any dirt or liquids into the housing interior. Type A is supplied with four additional countersunk sealing screws, which feature a polyamide coating on the head to create a tight seal.

see also...

- Ergostyle® Gripping Trays EN 733 (Technopolymer Plastic, Screw-In Type)
- Ergostyle® Gripping Trays EN 731 (Technopolymer Plastic, Clip-In Type)

How to order

GN 7330-127-A-2-SW

1	Length l_1
2	Type
3	Identification no.
4	Finish