



SS Stainless Steel

4 Type

K With tapped insert

Specification

1

5

- Hand knob  
Plastic  
Duroplast (Phenolic PF)  
Black, shiny finish
- Tapped insert  
- Steel, zinc plated,  
blue passivated finish
- Brass
- Stainless steel AISI 304

KU

MS

NI

- Hand knob  
Plastic  
Technopolymer (Polyamide PA)  
- Shock-resistant  
- Black, matte finish
- Tapped insert  
Steel, zinc plated,  
blue passivated finish

KT

• RoHS compliant

Information

DIN 6335 hand knobs with plain bore H7 are available under the GN 6335.1 / GN 6335.2 series.

see also...

- Hand Knobs DIN 6335 (Cast Iron / Stainless Steel / Aluminum)
- Hand Knobs GN 6335.1 (Phenolic Plastic, with Protruding Hub)
- Hand Knobs GN 6335.2 (Technopolymer Plastic, with Protruding Hub)
- Hand Knobs DIN 6335 with Loss Protection GN 111.7

How to order (Inch, Technopolymer, steel insert)

1 2 3 4

DIN 6335-KT-40-5/16X18-K

1 Material

2 Handle diameter  $d_1$

3 Thread  $d_2$

4 Type

How to order (Metric, Duroplast, stainless steel insert)

1 2 3 4 5

DIN 6335-KU-50-M10-K-NI

1 Material

2 Handle diameter  $d_1$

3 Thread  $d_2$

4 Type

5 Insert material

### Inch table

Dimensions in: inches - *millimeters*

d <sub>1</sub>	d <sub>2</sub>		d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.
	Plastic KU Steel insert	Plastic KT Steel insert				
1.26 32	-	1/4 x 20	0.55 14	0.79 20	0.39 10	0.47 12
1.57 40	1/4 x 20	5/16 x 18	0.71 18	0.98 25	0.51 13	0.55 14
1.97 50	-	3/8 x 16	0.87 22	1.26 32	0.79 20	0.71 18
2.48 63	-	1/2 x 13	1.02 26	1.57 40	0.98 25	0.87 22

### Metric table

Dimensions in: millimeters - *inches*

d <sub>1</sub>	d <sub>2</sub>				d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.	
	Plastic KU Steel insert	Plastic KU Brass insert MS	Plastic KU Stainless steel insert NI	Plastic KT Steel insert				Steel insert Brass insert	Stainless steel insert
20 0.79	-	M 4	-	-	10 0.39	13 0.51	6 0.24	7 0.28	-
25 0.98	M 5	M 5	M 5	-	13 0.51	17 0.67	8 0.31	9.5 0.37	7.5 0.30
32 1.26	M 6	M 6	M 6	M 6	14 0.55	20 0.79	10 0.39	12 0.47	9 0.35
40 1.57	M 8	M 8	M 8	M 8	18 0.71	25 0.98	13 0.51	14 0.55	12 0.47
50 1.97	M 10	M 10	M 10	M 10	22 0.87	32 1.26	20 0.79	18 0.71	15 0.59
63 2.48	M 12	M 12	M 12	M 12	26 1.02	40 1.57	25 0.98	22 0.87	18 0.71
80 3.15	M 16	M 16	M 16	M 16	35 1.38	50 1.97	30 1.18	30 1.18	24 0.94
100 3.94	M 20	-	-	-	34 1.34	65 2.56	38 1.50	30 1.18	-

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

