



Countersunk sealing screws /
Housing seal
(for identification no. 2)



2 Type

- A** Mounting from the operator's side
(for identification no. 2 with four
countersunk sealing screws)
- C** Mounting from the back

3 Identification no.

- 1** Without seal
- 2** With seal

Metric table

Dimensions in: millimeters - inches

l₁	h₁	h₂	l₂	l₃	l₄	l₅	l₆ +1	l₇ +1	m₁	m₂
127 5.00	80 3.15	43 1.69	72 2.83	25 0.98	3.5 0.14	22.5 0.89	60 2.36	88 3.46	100 3.94	53 2.09
155 6.10	80 3.15	43 1.69	99 3.90	25 0.98	3.5 0.14	22.5 0.89	60 2.36	115 4.53	128 5.04	53 2.09

Specification

- Zinc die-cast
Powder coated
Black, RAL 9005, textured finish **● SW**
Silver, RAL 9006, textured finish **● SR**
- Housing seal (Identification no. 2)
Black NBR rubber, glued
- Countersunk sealing screws DIN 7991 M5x16
(Type A, Identification no. 2)
- Stainless steel A2
- Polyamide coating on head
- Threaded studs (Type C)
- Stainless steel A2
- Molded-in
- Protection class IP 66
- IP Protection Classes → page 2130
- RoHS compliant

Information

- GN 7330 gripping trays can be easily and quickly installed from the front using countersunk screws or from the back with threaded studs.
- Gripping trays with housing seal (identification no. 2) prevent the penetration of any dirt or liquids into the housing interior. Type A is supplied with four additional countersunk sealing screws, which feature a polyamide coating on the head to create a tight seal.
- see also...
- Gripping Trays EN 733 (Technopolymer Plastic, Screw-In Type) → page 200
 - Gripping Trays EN 731 (Technopolymer Plastic, Clip-In Type) → page 198

How to order	1 Length l₁
	2 Type
	3 Identification no.
	4 Finish

GN 7330-127-A-2-SW