



SS Stainless Steel

4 Type

- A** With lanyard ring only
- H** With retaining cable
- K** With ball chain

Metric table

d ₁	d ₂ Thread	Length l				d ₃	h ₁	h ₂	h ₃	r	s	t min.
		10	15	20	25							
25* 0.98	M 5	0.39	0.59	0.79	0.98	12 0.47	16 0.63	8 0.31	2.5 0.10	21.2 0.83	2.8 0.11	-
32 1.26	M 6	0.63	0.79	0.98	1.18	14 0.55	20 0.79	10 0.39	3.5 0.14	22.3 0.88	2.8 0.11	12 0.47
40 1.57	M 8	0.79	0.98	1.18	1.57	18 0.71	25 0.98	13 0.51	4 0.16	29.5 1.16	3.2 0.13	14 0.55
50 1.97	M 10	0.79	0.98	1.18	1.77	22 0.87	32 1.26	17 0.67	5 0.20	34.6 1.36	3.8 0.15	18 0.71
63 2.48	M 12	1.18	1.57	1.97	-	26 1.02	40 1.57	21 0.83	5.5 0.22	36.7 1.44	3.8 0.15	22 0.87

Dimensions in: millimeters - inches

*This size is only available with threaded stud

Specification

- Star knob DIN 6336
Plastic
Technopolymer (Polyamide PA)
Black, matte finish
- Tapped insert
Stainless steel
European Standard No. 1.4305 (AISI 303)
- Threaded stud
Stainless steel
- M5 - M10:
European Standard No. 1.4567 (AISI 304 Cu)
- M12:
European Standard No. 1.4305 (AISI 303)
- Lanyard ring GN 111.6
Stainless steel
European Standard No. 1.4310 (AISI 301)
- Ball chain GN 111.5 (Type K)
Stainless steel
European Standard No. 1.4310 (AISI 301)
- Retaining cable GN 111.2 (Type H)
Stainless steel
European Standard No. 1.4301 (AISI 301)
Coated with clear plastic
- RoHS compliant

Information

GN 6336.13 star knobs with loss protection can be attached to a base element with the help of a ball chain or a retaining cable.

The star knobs are supplied ready assembled (with lanyard ring, with lanyard ring and retaining cable, or with lanyard ring and ball chain).

see also...

- Ball Chains GN 111.5 (Stainless Steel)
- Retaining Cables GN 111.2
- Spiral Retaining Cables GN 111.4
- Lanyard Rings GN 111.6
- More Star Knobs with Loss Protection GN 111.7

On request

- Ball chains / retaining cables with other lengths
- With spiral retaining cable GN 111.4
- Other GN series with loss protection
- Inch sizes

<p>How to order (Tapped insert)</p> <p>GN 6336.13-40-M8-A</p>	1	Handle diameter d ₁
	2	Thread d ₂
	4	Type
<p>How to order (Threaded stud)</p> <p>GN 6336.13-50-M10-30-K</p>	1	Handle diameter d ₁
	2	Thread d ₂
	3	Length l
	4	Type