



ELESA original design MBT+I



**3 Type**

D With mini revolving handle

Dimensions in: millimeters - inches

**Metric table**

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> H9 Bore	d <sub>3</sub>	d <sub>4</sub> Thread	d <sub>5</sub>	b	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	r
40 1.57	B 6	17 0.67	M 4	13.5 0.53	14 0.55	26.5 1.04	14 0.55	20 0.79	4 0.16	12.5 0.49
50 1.97	B 6	20 0.79	M 5	13.5 0.53	17 0.67	33 1.30	18 0.71	20 0.79	5 0.20	16.5 0.65
60 2.36	B 8	23 0.91	M 5	16 0.63	20.5 0.81	39 1.54	20 0.79	23 0.91	6 0.24	20.5 0.81
70 2.76	B 10	24 0.94	M 5	16 0.63	21.5 0.85	42 1.65	25 0.98	23 0.91	6 0.24	25 0.98
85 3.35	B 10	29 1.14	M 5	16 0.63	20 0.79	30.5 1.20	22 0.87	23 0.91	6 0.24	32.5 1.28
100 3.94	B 10	35 1.38	M 5	16 0.63	20 0.79	31 1.22	22 0.87	23 0.91	6 0.24	40 1.57

**Specification**

- Knob body  
Plastic  
Technopolymer (Polypropylene PP)  
- Reinforced, shock-resistant  
- Temperature resistant up to 194 °F (90 °C)  
- Black, matte finish
- Color of the cover cap (matte finish)
 

Black, RAL 9005	—
Orange, RAL 2004	<b>DOR</b>
Gray, RAL 7035	<b>DGR</b>
Yellow, RAL 1021	<b>DGB</b>
Blue, RAL 5024	<b>DBL</b>
Red, RAL 3000	<b>DRT</b>
Green, RAL 6017	<b>DGN</b>
- Hub bushing  
Brass
- Set screw DIN 916  
with internal hexagon and serrated point
- Mini revolving handle EN 595  
Plastic  
Technopolymer (Polyamide PA)  
- Black, matte finish  
- Threaded spindle  
Steel, zinc plated, blue passivated finish
- RoHS compliant

**Information**

EN 735 knurled control knobs are used for adjustments on specific operations requiring low torque only. Coarse adjustment can be achieved via the mini revolving handle (finger grip), while fine adjustment is performed by using the rim of the wheel.

see also...

- Knurled Control Knobs GN 736 (Aluminum, Black Anodized Finish)
- Knurled Control Knobs GN 736.1 (Aluminum, Black Anodized Finish)
- Control Knob Flanges GN 826 (for Adjustable Spindles)

How to order (With black cover cap)	<b>1 Knob diameter d<sub>1</sub></b>
<b>1</b> <b>2</b> <b>3</b>	<b>2 Bore d<sub>2</sub></b>
<b>EN 735-40-B6-D</b>	<b>3 Type</b>

How to order (With colored cover cap)	<b>1 Knob diameter d<sub>1</sub></b>
<b>1</b> <b>2</b> <b>3</b> <b>4</b>	<b>2 Bore d<sub>2</sub></b>
<b>EN 735-60-B8-D-DRT</b>	<b>3 Type</b>
	<b>4 Color of the cover cap</b>